

[-Click to Print-](#)

You are here: [Home](#) > [H.I.D.](#) > [Metal Halide](#) > [Open Rated](#) > 26586C

ITEM#: 26586C



Item#: 26586C
Industry Desc.: MP400W/U/UVP/BT37/PS/4K
Watts: 400
Avg. Life Hours: 17,000
Shape: BT37
Base Type: EX39 Excl. Mogul
Base Material: Nickel Plated Brass
Finish: Clear
Kelvin: 4000
CRI: 75
Package Qty: 1
Case Qty: 6
Additional Info: THIS OPEN RATED METAL HALIDE LAMP IS DESIGNED TO MEET CURRENT NEC REQUIREMENTS FOR OPERATION IN OPEN FIXTURES. THIS LAMP IS DESIGNED TO HELP CONTAIN HOT PARTICLES IN THE EVENT OF AN ARC TUBE RUPTURE.