



Dependable Power for Any Application

Product Datasheet

200/220/440 Primary Volts - 23/110 Secondary Volts - 1Ø - CE Marked Industrial Control Transformer - Encapsulated

Catalog #: CE020250



PRODUCT FEATURES

- UL and cUL listed
- UL and cUL listed, CE Marked
- CE Marked
- Constructed out of electrical lamination with precision wound coils
- Constructed out of electrical lamination with precision wound coils
- Fully encapsulated core and coil
- Available Fuse Kits and Accessories
- Covered under Acme's 10 year limited warranty

BENEFITS

- Molded terminal blocks with isolation barriers
- Dual labeling for easy product identification
- Heavy gauge steel mounting feet
- Fast wire connection terminal

UL STANDARD

UL 506

CSA STANDARD

C22.2 No 66

WARRANTY

GENERAL PRODUCT INFORMATION

VA:	250
Primary Voltage:	200/220/440
Secondary Voltage:	23/110
Frequency:	50/60 Hz
Max Temperature Rise:	55°C
UL Insulation Class:	105°C

PRODUCT MEASUREMENTS

Height (In./cm):	4.03 (10.2)
Width (In./cm):	4.50 (11.4)
Depth (In./cm):	4.78 (12.1)

CONFIGURATION

Mounting Type:	Floor
Wiring Diagram:	CE02

PACKAGING

Ship Weight (Lbs/Kg):	9.7 (4.4)
-----------------------	-----------

COMPLIANCES

UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No 66
CSA Listed:	LR7357-16
CE:	CE Marked
Warranty:	Acme Electric Warranty Card www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf