



Dependable Power for Any Application

Product Datasheet

460Δ Primary Volts - 230Y/133 Secondary Volts - 3Ø Drive Isolation Transformer - Three Phase

Catalog #: DTGA0514S



PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R with optional Weather Shield
- Aluminum foil windings
- Copper bus bar terminations
- Wound/Distributed core construction
- Covered under Acme's 10 year limited warranty
- Optional Thermal Switch - part # PL79900
- Optional wall mounting kit - part # PL79912

BENEFITS

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units

UL STANDARD

UL 1561

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

| | |
|-----------------------|----------|
| kVA: | 51.00 |
| Primary Voltage: | 460Δ |
| Secondary Voltage: | 230Y/133 |
| Frequency: | 60 Hz |
| ANFC Taps: | 2 |
| BNFC Taps: | 2 |
| Taps % Steps: | 2.5% |
| Max Temperature Rise: | 150°C |
| UL Insulation Class: | 220°C |

PRODUCT MEASUREMENTS

| | |
|------------------|--------------|
| Height (In./cm): | 29.9 (75.9) |
| Width (In./cm): | 28.15 (71.5) |
| Depth (In./cm): | 22.37 (56.8) |

CONFIGURATION

| | |
|--------------------|------------|
| Construction Type: | Ventilated |
| Mounting Type: | Floor |
| Weather Shield: | WSA2 |
| Wiring Diagram: | 38 |

PACKAGING

| | |
|-----------------------|-------------|
| Ship Weight (Lbs/Kg): | 400 (181.0) |
|-----------------------|-------------|

COMPLIANCES

| | |
|---------------|--|
| UL Standard: | UL 1561 |
| UL Listed: | File E12547 |
| CSA Standard: | C22.2 No. 47 |
| CSA Listed: | LR7357-32 |
| Warranty: | Acme Electric Warranty Card |
| | www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf |