



Dependable Power for Any Application

# Product Datasheet

## 575Δ Primary Volts - 460Y/266 Secondary Volts - 3Ø Drive Isolation Transformer - Three Phase

Catalog #: DTHB03304S



### PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R with optional Weather Shield
- Aluminum foil windings
- Aluminum bus bar terminations
- Butt stacked/Step lap core construction
- Covered under Acme's 10 year limited warranty
- Optional Thermal Switch - part # PL79900

---

### BENEFITS

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units

---

### UL STANDARD

UL 1561

---

### CSA STANDARD

C22.2 No. 47

---

### WARRANTY

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

## GENERAL PRODUCT INFORMATION

kVA:	330.00
Primary Voltage:	575Δ
Secondary Voltage:	460Y/266
Frequency:	60 Hz
ANFC Taps:	2
BNFC Taps:	2
Taps % Steps:	2.5%
Max Temperature Rise:	150°C
UL Insulation Class:	220°C

## PRODUCT MEASUREMENTS

Height (In./cm):	45.6 (115.8)
Width (In./cm):	39.5 (100.3)
Depth (In./cm):	35.5 (90.2)

## CONFIGURATION

Construction Type:	Ventilated
Mounting Type:	Floor
Weather Shield:	WSA5
Wiring Diagram:	44

## PACKAGING

Ship Weight (Lbs/Kg):	2091 (948.0)
-----------------------	--------------

## COMPLIANCES

UL Standard:	UL 1561
UL Listed:	File E12547
CSA Standard:	C22.2 No. 47
CSA Listed:	LR7357-32
Warranty:	Acme Electric Warranty Card
	<a href="http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf">www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf</a>