



Dependable Power for Any Application

# Product Datasheet

## 200/220/240 Primary Volts - 115 Secondary Volts - 1Ø Appliance Transformers - Single Phase

Catalog #: T160833



### PRODUCT FEATURES

- Meets NEMA standard
- UL Type 3R Enclosure
- Primary Plug and Secondary Receptacle
- Constructed out of electrical lamination with precision wound coils
- Encapsulated autotransformer construction
- Covered under Acme's 10 year limited warranty

---

### WARRANTY

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

### GENERAL PRODUCT INFORMATION

VA:	500
Primary Voltage:	200/220/240
Secondary Voltage:	115
Frequency:	50/60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

### PRODUCT MEASUREMENTS

Height (In./cm):	9.68 (24.6)
Width (In./cm):	4.75 (12.1)
Depth (In./cm):	4.51 (11.5)

### CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall
Connections (Ft./m):	6 (1.8) primary cord and secondary receptacle

**PACKAGING**

Ship Weight (Lbs/Kg): 10 (4.5)

**COMPLIANCES**

Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

