



Dependable Power for Any Application

Product Datasheet

240 X 480 Primary Volts - 120 Secondary Volts - 1Ø Industrial Control Transformer - Harsh Environment

Catalog #: T181221



PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R epoxy encapsulated
- Fully encapsulated core and coil
- Wall Mounted
- Voltage Regulation exceeds NEMA requirements
- Covered under Acme's 10 year limited warranty

BENEFITS

- Designed for outside control panel installation

UL STANDARD

- UL 506

CSA STANDARD

- C22.2 No 47

WARRANTY

- Acme Electric Warranty Card
- www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

- | | |
|--------------------|-----------|
| VA: | 5000 |
| Primary Voltage: | 240 X 480 |
| Secondary Voltage: | 120 |

Frequency:	50/60 Hz
Max Temperature Rise:	55°C
UL Insulation Class:	155°C

PRODUCT MEASUREMENTS

Height (In./cm):	13.85 (35.2)
Width (In./cm):	13.25 (33.7)
Depth (In./cm):	10.19 (25.9)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall
Wiring Diagram:	B

PACKAGING

Ship Weight (Lbs/Kg):	140 (63.5)
-----------------------	------------

COMPLIANCES

UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No 47
CSA Listed:	LR7357-32
Warranty:	Acme Electric Warranty Card
	www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf