



Dependable Power for Any Application

# Product Datasheet

## Autotransformer - 600/480 Primary Volts - 480/380 Secondary Volts - 3Ø Dry Type Distribution Transformer - Three Phase

Catalog #: T2A527191



### PRODUCT FEATURES

- UL listed, CSA certified
- Fully encapsulated core and coil
- UL Type 3R epoxy encapsulated
- Floor Mounted
- Ground Studs for use with non-metallic conduit
- Aluminum Bus termination
- Covered under Acme's 10 year limited warranty

---

### BENEFITS

- Quiet operation with sound levels below NEMA standards

---

### UL STANDARD

- UL 1561

---

### CSA STANDARD

- C22.2 No. 47

---

### WARRANTY

- Acme Electric Warranty Card
- [www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

### GENERAL PRODUCT INFORMATION

kVA:	500/400
Primary Voltage:	600/480
Secondary Voltage:	480/380
Frequency:	50/60 Hz
ANFC Taps:	-
BNFC Taps:	2
Taps % Steps:	5.0%
Max Temperature Rise:	150°C
UL Insulation Class:	220°C

#### PRODUCT MEASUREMENTS

Height (In./cm):	35.47 (90.1)
Width (In./cm):	31.90 (81.0)
Depth (In./cm):	26.88 (68.3)

#### CONFIGURATION

Construction Type:	Ventilated
Mounting Type:	Floor
Weather Shield:	WSA3
Wiring Diagram:	57

#### PACKAGING

Ship Weight (Lbs/Kg):	790 (358.3)
-----------------------	-------------

#### COMPLIANCES

UL Standard:	UL 1561
UL Listed:	File E12547
CSA Standard:	C22.2 No. 47
CSA Listed:	LR7357-32
Warranty:	Acme Electric Warranty Card <a href="http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf">www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf</a>

