



Dependable Power for Any Application

# Product Datasheet

190/200/208/220 X 380/400/416/440 Primary Volts - 110/220  
Secondary Volts - 1Ø - CE Marked  
Dry Type Distribution Transformer - Single Phase

Catalog #: TF279267S



## PRODUCT FEATURES

- UL listed, CSA certified
- Meet CSA C802.2 Efficiency
- Fully encapsulated core and coil
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

---

## BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

---

## UL STANDARD

UL 506

---

## CSA STANDARD

C22.2 No. 47

---

## CE

CE Marked

Acme Electric Warranty Card

---

## WARRANTY

[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

## GENERAL PRODUCT INFORMATION

kVA:	25.00
Primary Voltage:	190/208/220/240 x 380/416/440/480
Secondary Voltage:	120/240
Frequency:	50/60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

## PRODUCT MEASUREMENTS

Height (In./cm):	18.44 (46.8)
Width (In./cm):	16.13 (41.0)
Depth (In./cm):	13.34 (33.9)

## CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall
Knockouts (In./Cm):	1.00-1.50 (2.5-3.8)
Wiring Diagram:	64

## PACKAGING

Ship Weight (Lbs/Kg):	300 (136.0)
-----------------------	-------------

## COMPLIANCES

UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No. 47
CSA Listed:	LR7357-32
CE:	CE Marked
Warranty:	Acme Electric Warranty Card
	<a href="http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf">www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf</a>