

Catalog Number: 15PCJ1K2300
Product ID: 7TAA123100R0077
UPC Number: 78378663622
Status: Active

15kV Power Cable Joint Style 1 with Single Piece Housing, Cable Insulation Diameter 1.090 inch to 1.310 inch. Copper Conductor. Conductor Size AWG Stranded 350.

North American Specifications (UNSPSC)

UNSPSC	39121452 Cable joint
IGCC	4677 Cable joint
Brand Name	Elastimold
Type	Power Cable Joint
Special Features	Power Cable Joints utilize permanently crimped connectors. PCJ housings are fully insulated, shielded and sealed for direct-burial, vault, submersible and other severe service applications. Units have been designed and tested per IEEE Standard 404 to ensure system matched performance and ratings equal to the cable to which the splice will be installed. Power Cable Joints are available in two styles. Style 1 uses a single-piece housing that is sized to accommodate a specific range of cable - ideally suited to straight splicing of the same or similar cable. Style 2 designs incorporate a universal housing with separate cable adapters to allow transition splices of different types and sizes of cable.
Application	For Direct Burial, Vault, Submersible and Other Severe Service Applications.
Standard	IEEE Standard 404
Size	14-3/8 inch long
Connection	Compression
Conductor Range	Conductor Size AWG Stranded 350.
Number Of Conductors	2
Material	EPDM Rubber
Color	Black
Voltage Rating	15kV
Insulation	Yes

Packaging

Outer Quantity	15
Weight Uom	224.5 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com