



Representative

Catalog Number: 166LR-B-5240
Product ID: 7TAA121100R0092
UPC Number: 78378663259
Status: Obsolete
Replacement Catalog: 162LR-B-5240

15kV 200 Amp, Loadbreak Elbow Connector with Test Point, Cable Insulation Diameter 0.635 inch to 0.905 inch. Bi-Metal Compression Lug. Conductor Size AWG Compressed Stranded 1/0 /Solid 2/0 /mmSquared 53.49.

North American Specifications (UNSPSC)

UNSPSC	39121421 Electrical connector assembly
IGCC	4586 Electrical connector assembly
Brand Name	Elastimold
Type	Elbow Connector with Test Point
Special Features	Includes 02500X Long Bi-Metal Lug as Standard.
Conductor Range	AWG Compressed Stranded 1/0 /Solid 2/0 /mm-Squared 53.49
Material	EPDM Rubber
Voltage Rating	15kV
Amperage Rating	200 Amp
Insulation	Yes

Packaging

Inner Quantity	1
Inner Dimensions (inches)	10.5x10.5x3
Outer Quantity	15
Outer Dimensions (inches)	19x13x11
Weight Uom	2.07 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com