



Actual

Catalog Number: 2B40
Product ID: 7TAH006160R0015
UPC Number: 78378640003
Status: Active

Copper Type 2B - Two-Bolt Connector without Spacer for Wire Range Main: 1/0 - 4/0 Str.
 Tap: 6 Sol. - 4/0 Str. , Bolt Size 9/16

- Castings and bolts of high-strength copper alloy. Removable cap.
- UL 486A listed for copper conductor only.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Two-Bolt Connector
Special Features	Castings and bolts of high-strength copper alloy. Removable cap.
Standard	UL E9809
Material	Copper
Conductor Range (Main/Primary)	1/0 - 4/0 Str.
Conductor Range (Tap/Secondary)	6 Sol. - 4/0 Str.
Bolt Size	42994

European Specifications (ETIM)

ETIM	EC000491 Earth terminal clamp
Suitable for	Round conductor
Material	Copper

Packaging

Inner Dimensions (inches)	6.9x4.69x5.2
Outer Quantity	25
Outer Dimensions (inches)	10x5.2x3.5
Weight Uom	35 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com