



Actual

**Catalog Number:** APS41  
**Product ID:** 7TAH006130R0009  
**UPC Number:** 78378620145  
**EAN Number:** 05414363147985  
**Status:** Active

Type APS Tin-Plated Aluminum Dual-Rated Split-Bolt Connector for Use on Copper, Aluminum Conductors. Conductor Range for Equal Main and Tap 4/0-2 Str.

- Installs with standard wrenches.
- Splicing, tapping or terminating conductors in power and grounding electrical connection.

#### North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Split-Bolt
Special Features	Installs with standard wrenches.
Application	Splicing, tapping or terminating conductors in power and grounding electrical connection.
Standard	UL E9809
Material	Aluminum
Finish	Electro Tin-Plated

#### European Specifications (ETIM)

ETIM	EC000491 Earth terminal clamp
Suitable for	Round conductor
Material	Copper

#### Packaging

Inner Quantity	25
Inner Dimensions (inches)	7.2x6.2x4.9
Outer Quantity	150
Outer Dimensions (inches)	20.5x11.5x7.6
Weight Uom	23.5 lbs. per 100

#### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com