



Actual

Catalog Number: ASR0214
Product ID: 7TAH006620R0029
UPC Number: 78378613321
Status: Active

Type ASR-ALCUL Splice Reducer with Solid Barrier Wire Stop for Conductor Range Max 2 Str., Min 14 AWG

- Easy Installation - no special tools required.

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Dual-Rated
Special Features	Easy Installation - no special tools required.
Standard	UL E9809
Conductor Range	2/0 Str-14 AWG
Material	Aluminum
Finish	Tin Plated

Packaging

Inner Quantity	12
Inner Dimensions (inches)	5x3.5x6.5
Outer Quantity	120
Outer Dimensions (inches)	13.4x10.7x7
Weight Uom	3 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com