



Actual

Catalog Number: ASR2506
Product ID: 7TAH006620R0031
UPC Number: 78378613323
Status: Active

Type ASR-ALCUL Splice Reducer with Solid Barrier Wire Stop for Conductor Range Max 250 kcmil, Min 6 Str.

- Easy Installation - no special tools required.

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Dual-Rated
Special Features	Easy Installation - no special tools required.
Standard	UL E9809
Conductor Range	250 kcmil-6 Str
Material	Aluminum
Finish	Tin Plated

Packaging

Outer Quantity	12
Outer Dimensions (inches)	6.2x4.1x4.3
Weight Uom	12 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com