



Actual

Catalog Number: JAB34
Product ID: 7TAA014200R0010
UPC Number: 78378680071
EAN Number: 05414363153245
Status: Active

Ground Rod Clamps Type JAB , Rod Size 3/4, Wire Range 8 Sol - 1/0 Str, Socket Set Screw

- Cast of high-strength corrosion-resistant copper alloy. UL listed for direct burial.
- Both hex head bolts and socket set screws available.

North American Specifications (UNSPSC)

UNSPSC	39121613 Grounding devices or assemblies
IGCC	4909 Grounding devices or assemblies
Brand Name	Blackburn
Type	Ground Rod Clamps
Special Features	Cast of high-strength corrosion-resistant copper alloy. UL listed for direct burial.
Standard	UL E3060, CSA 29625
Conductor Size	8 Sol - 1/0 Str
Conductor Material	Copper

Packaging

Inner Quantity	50
Inner Dimensions (inches)	5x4.37x6.5
Outer Quantity	400
Outer Dimensions (inches)	19x11x8
Weight Uom	12 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000478

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com