



Representative

**Catalog Number:** LCN300  
**Product ID:** 7TAH007800R0051  
**UPC Number:** 78378603264  
**Status:** Active

Type LCN Copper Two-Hole Lug, Long Barrel, Max 35kV, Wire Size 300 kcmil, 1/2 Inch Bolt Hole, Tin Plated, Die Color Code White

- Made of high-conductivity seamless copper tubing. Tin plated for corrosion resistance.
- Specifically chamfered barrel for ease of installation.
- Color-coded for matching die identification.

### North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Blackburn
Type	Long Barrel Copper Lug
Special Features	Made of high-conductivity seamless copper tubing. Tin plated for corrosion resistance.
Standard	UL E9809
Cable Size	300 kcmil
Stud Size	1/2 Inch
Number Of Holes	2
Material	Copper
Color	White

### European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
Insulated	N
With sight-hole	N
Material	Copper
Surface protection	Tinned
Number of fixing holes	2

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	100
Outer Dimensions (inches)	5.5x4.7x3.2
Weight Uom	30 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)