



Representative

Catalog Number: PKL66-1
Product ID: 7TAA267280R0016
UPC Number: 78378604704
Status: Active

Compression Pin Terminal Aluminum, Contax filled for Wire Range 4/0 ASCR, 4/0 Stranded, Pigtail: 0.365 x 6, Mechanical Dies: 840, K840, TX, Hydraulic Dies: 840, B48EA, EEI 11A, K840, U249, 76

North American Specifications (UNSPSC)

UNSPSC	39121458 Wire or cable compression reducer
IGCC	4685 Wire or cable compression reducer
Brand Name	Blackburn
Type	Pigtail Compression Sleeve
Special Features	Sleeves are Highly Conductive Aluminum. Pigtails are Solid Copper, Tin-Plated. Installed with Standard Tools and Dies. Prefilled with Oxide Inhibitor.
Application	Designed for use in joining Aluminum Secondaries and Services to Copper Transformer Bushings
Size	Sleeve Length 3-1/2 inches
Reduced Size	Pigtail: 0.365 x 6 inch
End Connection	Compression
Reduced End Connection	Compression
Conductor Size	Wire Range 4/0 ASCR, 4/0 Stranded
Number Of Conductors	2
Material	Aluminum Sleeve, Pre-attached Copper Pigtail
Finish	Tinplated Pigtail
Voltage Rating	35kV
Insulation	None
Mounting	None

Packaging

Inner Quantity	25
Inner Dimensions (inches)	10.9x5.7x3.4
Outer Quantity	150
Outer Dimensions (inches)	20x11.2x7.5
Weight Uom	44 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com