



Actual

Catalog Number: VGC68
Product ID: 7TAH006170R0006
UPC Number: 78378629841
Status: Active

Bronze ViceLock Parallel Groove Connector for 2 Conductors Wire Range 10 Sol. To 6 Sol.

- Installs quickly and easily with no need for special or heavy tools. Vibration-resistant. Full thread engagement design increases bolt strength. High pressure/torque ratio ensures a low electrical resistance connection.
- Helps reduce inventory by accepting a wide range of conductors. Larger sizes include stainless steel hardware.
- Distribution loads, service bonding, tap and ground connections.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Parallel Groove Connector
Special Features	Installs quickly and easily with no need for special or heavy tools. Vibration-resistant. Full thread engagement design increases bolt strength. High pressure/torque ratio ensures a low electrical resistance connection.
Application	Distribution loads, service bonding, tap and ground connections.
Material	Bronze

Packaging

Inner Quantity	50
Inner Dimensions (inches)	4.63x7.25x5.25
Outer Quantity	250
Outer Dimensions (inches)	24x5.75x7.75
Weight Uom	8.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com