

Switch Type	MICRO SWITCH™ Standard 25,4 mm H x 17,8 mm W x 50,8 mm L [1.0 in H x 0.7 in W x 2.0 in L]
Sealed	No
Ampere Rating	15 A
Circuitry	SPDT
Actuator	Overtravel Plunger
Termination	Solder
Operating Temperature	-55 °C to 85 °C [-67 °F to 185 °F]
Voltage	125 Vac
Contact Type	Silver
Operating Force (OF)	2,5 N to 3,61 N [9.0 oz to 13.0 oz]
Release Force	1,11 N [4.0 oz] min.
Pretravel (PT)	0,38 mm [0.015 in] max.
Overtravel (OT)	3,18 mm [0.125 in] min.
Differential Travel (DT)	0,01 mm to 0,05 mm [0.0004 in to 0.0020 in]
Operating Position (OP)	48,4 mm ±0,50 mm [1.906 in ±0.020 in]
Material	Plastic
Housing Material	General Purpose Phenolic
Agency Approvals and Standards	UL, CE, CSA
Mounting Screw Size	3,53 mm [0.139 in]
Mounting Centers	25,4 mm [1 in]
Tightening Torque	0,33 N m [3.0 in lb]
Weight	39 g [0.086 lb]
Package Height	24,1 mm [0.95 in]
Package Width	17,5 mm [0.69 in]
Package Length	49,3 mm [1.94 in]
Recommended For	Furnished with unassembled seal boot
Comment	CE: 61058-1; UL: E12252; CSA: LR41370
Availability	Global
UNSPSC Code	30211905
UNSPSC Commodity	30211905 Snap switches
Series Name	BZ/BA/WA/YZ