

Transformer (TSS693-22) Specification Sheet

Project Name:	Location:	MFG: Philips Hadco
Fixture Type:	Catalog No.:	Qty:



Ordering Guide

Example: TSS693-22

Product Code	TSS693-22	Transformer
--------------	-----------	-------------

Specifications

HOUSING:

Housing is 304 brushed stainless steel case with stainless steel screws and lockable captive door, hinged on side. 1/2" Knockout on one side for hardwiring or accessory mounting. Weather-proof compartment for plug-in time clock and photo cell.

ELECTRICAL ASSEMBLY:

6-ft heavy-duty 18-3 AWG, 105° C, SJT power cord with 3 prong grounded wall plug. Large wiring compartment. Large terminal blocks to accommodate up to four (4) #10 wires. Epoxy encapsulated toroidal transformer with built-in primary thermal protection. Magnetic circuit breaker for each 300W secondary circuit. 12V, 13V, 14V, 15V, 17V, 20V, and 22V output taps. Three (3) 1/2" knockouts for low-voltage exit, on bottom of housing. Handles 600 watts. 22 Volt Transformers are dimmable.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

WARRANTY:

Lifetime limited warranty.

Height :

17 5/8" (448mm)

Width:

6 3/16" (157mm)

Depth:

6 3/4" (171mm)

Max. Weight:

29 lb