

## ALUMINUM WOUND, THREE PHASE, NEMA 3R STYLE ENCLOSURE

Products listed on this page are available as 'CE Mark' products. Please consult our sales office.

**240 Delta Primary Volts                      480Y/277 Secondary Volts                      60 Hz**

kVA	Catalog Number	Case Style (Pages 254-257)	Approx. Dimensions (Inches)			Approx. Weight (Lbs.)	Mtg Type W - Wall F - Floor	Wiring Diagram (Pages 258-269)
			Width	Depth	Height			
15	MK015DK	UH1	16.75	14	22	180	F or W*	SCD 26
30	MK030DK	UH2	21.5	19.5	29	300	F or W*	SCD 34
45	MK045DK	UH2	21.5	19.5	29	400	F or W*	SCD 34
75	MK075DK	UH3	26	21	38	575	F or W*	SCD 34
112.5	MK112DK	UH3	26	21	38	750	F	SCD 34
150	MK150DK	UH4	30	24	39	900	F	SCD 34
225	MK225DK	UJ1	39.5	30	50	1350	F	SCD 34
300	MK300DK	UJ1	39.5	30	50	1550	F	SCD 34
500	MK500DK	UJ2	48.5	34	59	2400	F	SCD 26
750	MK750DK	UJ3	51.5	39	66	3450	F	No Taps

For shielded units, please add the suffix "S" to the above part numbers.

\*OPTIONAL WALL MOUNTING KIT REQUIRED.

**480 Delta Primary Volts                      208Y/120 Secondary Volts                      60 Hz**

kVA	Catalog Number	Case Style (Pages 254-257)	Approx. Dimensions (Inches)			Approx. Weight (Lbs.)	Mtg Type W - Wall F - Floor	Wiring Diagram (Pages 258-269)
			Width	Depth	Height			
9	MK009KB	UH1	16.75	14	22	140	F or W*	SCD 33
15	MK015KB	UH1	16.75	14	22	180	F or W*	SCD 33
30	MK030KB	UH2	21.5	19.5	29	300	F or W*	SCD 21
45	MK045KB	UH2	21.5	19.5	29	400	F or W*	SCD 21
75	MK075KB	UH3	26	21	38	575	F or W*	SCD 21
112.5	MK112KB	UH3	26	21	38	750	F	SCD 21
150	MK150KB	UH4	30	24	39	900	F	SCD 21
225	MK225KB	UJ1	39.5	30	50	1350	F	SCD 21
300	MK300KB	UJ1	39.5	30	50	1550	F	SCD 21
500	MK500KB	UJ2	48.5	34	59	2400	F	SCD 10
750	MK750KB	UJ3	51.5	39	66	3450	F	SCD 10

For shielded units, please add the suffix "S" to the above part numbers.

\*OPTIONAL WALL MOUNTING KIT REQUIRED.

**480 Delta Primary Volts                      240 Delta/120 CT<sup>1</sup> Secondary Volts                      60 Hz**

kVA	Catalog Number	Case Style (Pages 254-257)	Approx. Dimensions (Inches)			Approx. Weight (Lbs.)	Mtg Type W - Wall F - Floor	Wiring Diagram (Pages 258-269)
			Width	Depth	Height			
9	MK009KD	UH1	16.75	14	22	140	F or W*	SCD 13
15	MK015KD	UH1	16.75	14	22	180	F or W*	SCD 13
30	MK030KD	UH2	21.5	19.5	29	300	F or W*	SCD 23
45	MK045KD	UH2	21.5	19.5	29	400	F or W*	SCD 23
75	MK075KD	UH3	26	21	38	575	F or W*	SCD 23
112.5	MK112KD	UH3	26	21	38	750	F	SCD 23
150	MK150KD	UH4	30	24	39	900	F	SCD 23
225	MK225KD	UJ1	39.5	30	50	1350	F	SCD 23
300	MK300KD	UJ1	39.5	30	50	1550	F	SCD 23
500	MK500KD	UJ2	48.5	34	59	2400	F	SCD 15
750	MK750KD	UJ3	51.5	39	66	3450	F	SCD 15

For shielded units, please add the suffix "S" to the above part numbers.

\*OPTIONAL WALL MOUNTING KIT REQUIRED.

<sup>1</sup> No center tap is provided on the 9kVA unit. The 120V lighting tap is limited to 5% of nameplate rating.

Note: For three phase copper Encapsulated units, please refer to Section 12.

