

SPIRAL-LITE™

3-Way Compact Fluorescent Lamps



3-WAY

Features and Benefits

- 10,000-hour life
- Energy Star qualified
- Up to 75% energy savings compared to incandescent
- 82 CRI
- Works in standard 3-way fixtures to provide three different light output levels
- 1-year warranty

Applications

- General lighting
- Table lamps
- Floor lamps
- Ceiling fixtures
- 3-way fixtures

Save Energy in Specialty Fixtures with Spiral-Lite Low Profile 3-Way CFLs

Litetronics Spiral-Lite™ Low Profile (SPLP) 3-Way CFLs are specially engineered to provide quality light and energy savings in specialty fixtures. With the light output equivalence of a 50/100/150-watt incandescent lamp, the Spiral-Lite 3-Way lamp offers low, medium, and high light settings in the same fixture. Spiral-Lite 3-Way lamps are Energy Star qualified and work in standard 3-way fixtures.

Like all Litetronics Spiral-Lite lamps, the SPLP 3-Way CFLs reduce energy consumption by up to 75% and come with a 1-year warranty. With Spiral-Lite 3-Way CFLs, you no longer have to choose between energy savings and special feature lighting applications.

LITETRONICS®

235 East 171st Street
Harvey, Illinois 60426
www.Litetronics.com

SPIRAL-LITE™ LOW PROFILE Compact Fluorescent Lamps



3-WAY

3-WAY Compact Fluorescent Lamp

WATTS	BASE	VOLTS	DESCRIPTION	ORDERING CODE	QTY/ CASE	AVERAGE RATED LIFE	CRI	CCT(K)*	INITIAL LUMENS	MEAN LUMENS	M.O.L.**	M.O.D.***
12/22/33 \$	MED	120	33W SPLP 3-WAY 27	L-33627	40	10,000	82	2700	700/1500/2245	575/1275/1900	5.32"	2.75"

SPECIFICATIONS

INPUT LINE FREQUENCY	50/60 HZ
RELIABLE OPERATING TEMP.	0°F – 131°F
POWER FACTOR	> .50

CONVERSION CHART

CFL	=	INCANDESCENT
12/22/33-watt	=	50/100/150-watt

 Energy Star Qualified

\$ Energy Savings

* Correlated Color Temperature

** Maximum Overall Length (in inches)

*** Maximum Overall Diameter (in inches)

Not for use with dimmers or in totally enclosed fixtures.

