

Condulet® Conduit Outlet Bodies


Covers and Gaskets Dimensions Pgs. 9 to 11

Blank Covers



Sheet Steel

Size	Form 7 Wedgenut Cat. #	Form 8* Cat. #	Form 7 Snaptight™ Covers† Cat. #	Form 7 Wedgenut w/Integral Gasket Cat. #
1/2	170	180	170-SG	170G
3/4	270	280	270-SG	270G
1	370	380	370-SG	370G
1 1/4	470	480	470-SG	470G
1 1/2	570	580	570-SG	570G
2	670	680	670-SG	670G
2 1/2	870	880		
3	870	880		
3 1/2	970	980		
4	970	980		



Sheet Aluminum

Feraloy® Iron Alloy

Cast Aluminum

Size	Mark 9 Cat. #	Form 7 Wedgenut Cat. #	Form 8* Cat. #	Form 7 Wedgenut Cat. #
1/2	190	170F	180F	170F-SA
3/4	290	270F	280F	270F-SA
1	390	370F	380F	370F-SA
1 1/4	490	470F	480F	470F-SA
1 1/2	590	570F	580F	570F-SA
2	690	670F	680F	670F-SA
2 1/2	889	870F	880F	870F-SA
3	889	870F	880F	870F-SA
3 1/2	989	970F	980F	970F-SA
4	989	970F	980F	970F-SA

Solid Gaskets Neoprene



Form 7 Cat.

Size	Cat. #
1/2	GASK571
3/4	GASK572
1	GASK573
1 1/4	GASK574
1 1/2	GASK575
2	GASK576
2 1/2	GASK578
3	GASK578
3 1/2	GASK579
4	GASK579



Form 8* Cat.

Size	Cat. #
1/2	GASK851N
3/4	GASK852N
1	GASK853N
1 1/4	GASK854N
1 1/2	GASK805N
2	GASK806N
2 1/2	GASK808N
3	GASK808N
3 1/2	GASK809N
4	GASK809N



Form 9† Cat.

Size	Cat. #
1/2	GASK1941
3/4	GASK1942
1	GASK1943
1 1/4	GASK1944
1 1/2	GASK1945
2	GASK1946
2 1/2	GASK808N
3	GASK808N
3 1/2	GASK809N
4	GASK809N

* 1/2 - 1 1/4 are solid gaskets; 1 1/2 - 4 are open gaskets.

† 1/2 - 2 are solid gaskets; 2 1/2 - 4 are open gaskets.

* Two cover screws on 1/2" to 1 1/4" Form 8 covers and four cover screws on 1 1/2" and larger Form 8 covers.

‡ Form 7 Snaptight covers with integral sealing gasket are installed without the use of screws.