



HEAVY-DUTY POWER TOOLS

GUARANTEED TOUGH.

HAMMERDRILLS



SPECIFICATIONS	DWS11	DWS05	DWDS20/K	DWS25K
Amps	7.8 Amps	7.8 Amps	10.0 Amps	10.0 Amps
Max Watts Out	650 W	650 W	980 W	980 W
No Load Speed	0-2,700 rpm	0-1,100 / 0-2,700 rpm	0-1,200 / 0-3,500 rpm	0-1,200 / 0-3,500 rpm
Blows/Min	0-46,000 bpm	0-19,000 / 0-46,000 bpm	0-56,000 bpm	0-56,000 bpm
Capacity In Steel	1/2"	1/2"	1/2"	1/2"
Capacity In Wood	1-1/4"	1-1/2"	1-1/2"	1-1/2"
Concrete Optimum	5/32" - 3/8"	5/32" - 3/8"	5/32" - 7/16"	5/32" - 7/16"
Kit Box	No	No	No/Yes	Yes
Tool Length	11-1/2"	13"	14"	13"
Tool Weight	4.3 lbs	4.8 lbs	6.0 lbs	6.0 lbs

SDS ROTARY HAMMERS



SPECIFICATIONS	D25111K	D25113K	D25211K	D25213K
Optimal Concrete Drilling	5/32" - 5/8"	5/32" - 5/8"	5/32" - 5/8"	5/32" - 5/8"
Amps	8.0 Amps	8.0 Amps	8.0 Amps	8.0 Amps
Impact Energy	2.2 ft-lbs	2.5 ft-lbs	2.2 ft-lbs	2.5 ft-lbs
No Load Speed	0-1,150 rpm	0-1,150 rpm	0-1,150 rpm	0-1,150 rpm
Blows/Min	0-4,300 bpm	0-4,300 bpm	0-4,300 bpm	0-4,300 bpm
Chipping	No	Yes	No	Yes
Clutch	Yes - Factory Set	Yes - Factory Set	Yes - Factory Set	Yes - Factory Set
Tool Length	14.2"	14.2"	16.6"	16.6"
Tool Weight	5.6 lbs	5.7 lbs	5.9 lbs	6.1 lbs
Warranty - Service Contract	1 Yr	1 Yr	1 Yr	1 Yr



SPECIFICATIONS	D25313K	D25314K	D25404K
Optimal Concrete Drilling	5/32" - 5/8"	5/32" - 5/8"	3/8" - 7/8"
Amps	8.0 Amps	8.0 Amps	8.3 Amps
Impact Energy	2.5 ft-lbs	2.5 ft-lbs	3.34 ft-lbs
No Load Speed	0-1,150 rpm	0-1,150 rpm	0-730 rpm
Blows/Min	0-4,300 bpm	0-4,300 bpm	0-4,100 bpm
Chipping	Yes	Yes	Yes
Clutch	Yes - Factory Set	Yes - Factory Set	Yes - Factory Set
Tool Length	11.5"	12.1"	15.25"
Tool Weight	6.5 lbs	6.8 lbs	10.75 lbs
Warranty - Service Contract	1 Yr	1 Yr	1 Yr

DUST EXTRACTION



SPECIFICATIONS	D25300DH
Built In Motor	Yes
Shut Off Delay	Yes
Weight	3.3 lbs
HEPA Certified	Yes
Fits Models	D25303, D25304, D25313, D25314

SDS MAX ROTARY HAMMERS



SPECIFICATIONS	D25500K	D25600K	D25701K	D25730K
Optimal Concrete Drilling	3/8" - 1-1/4"	1/2" - 1-3/8"	5/8" - 1-9/16"	1" - 1-3/4"
Amps	11.0 Amps	11.5 Amps	13.0 Amps	15.0 Amps
Impact Energy	7.3 ft-lbs	8.0 ft-lbs	11.7 ft-lbs	15.0 ft-lbs
Vibration Control	No	No	Yes - SHOCKS™	Yes - SHOCKS™
No Load Speed	140-280 rpm	140-280 rpm	137-275 rpm	125-250 rpm
Blows/Min	1,330-2,660 bpm	1,330-2,660 bpm	1,260-2,520 bpm	1,150-2,304 bpm
Clutch	Yes - Factory Set	Yes - Factory Set	Yes - 2 Stage CTC®	Yes - 2 Stage CTC®
Tool Length	18.5"	18.5"	20.5"	23.0"
Tool Weight	13.0 lbs	13.4 lbs	17.5 lbs	19.2 lbs
Warranty - Service Contract	1 Yr	1 Yr	2 Yr	2 Yr

1-800-4 DEWALT

Text "DEWALT" to 32075 to be the first to know about anything DEWALT