

D28770K

Deep Cut Variable Speed Band Saw Kit



Product Features

- Rubber bumpers protect casting from jobsite abuse
- Lightweight and well-balanced design allows for more accurate cuts
- Innovative sight light allows user to see cut line in any jobsite environment
- Powerful 6.0 Amp motor designed to withstand jobsite applications
- 4-3/4" deep cut capacity for round or rectangular stock
- Dual bearing blade guide rollers increase durability in the blade support system
- Durable and adjustable material guide allows user to adjust for various jobsite materials
- Large front handle allows for more hand space and control
- Ergonomic soft grip back handle provides comfort during use
- Externally replaceable brushes allow for quick repairs on the jobsite
- Speed control knob allows user to tailor the blade speed for various applications
- Integrated hang hook allows user to hang the saw without damaging front handle or castings

Specifications

Amps	6.0Amps
Ft/Min	fpm
Max Capacity (Round)	4-3/4"
Max Capacity (Rectangular)	4-3/4"
Front Handle Style	Bale
LED Light	No
AC/DC Capability	No
Rubber Bumpers	No
Tool Length	21"
Tool Weight	15.0lbs

Warranty Information

This DEWALT® High Performance Industrial Tool comes with a warranty package that includes:

- 1 Year Free Service Contract
- 3 Year Limited Warranty
- 90 Day Money Back Guarantee

[More information on the general DEWALT warranty](#)

D28770K Includes:

- Hex Wrench
- standard 44-7/8"x1/2"x.020" blade
- Kit Box