



D55153

1.1 HP Continuous 4 Gallon Electric Hand Carry Compressor

Product Features

- 4.0 CFM delivered @ 90 PSI pump provides rapid recovery
- Oil lubricated pump improves durability
- Cast iron cylinder enhances pump life
- High-flow regulator for increased performance
- 4 gallon twin stack tank design with proven acceptance in the market
- Dual soft start valves assist in cold weather start-up

Specifications

Horsepower	1.1HP
Drive	Direct
Tank Size	4gal
Power Supply	120V AC, 15 amps, 60 Hz, 2 pole induction motor
CFM @ 100 PSI	3.8CFM
Pump Speed	3,400rpm
Tool Length	18"
Tool Width	18.5"
Tool Height	16.75"
Tool Weight	56.5lbs
Shipping Weight	60lbs

Warranty Information

This DEWALT® High Performance Industrial Tool comes with a warranty package that includes:

- 30 Day Money Back Guarantee
- 1 Year Free Service Contract
- 1 Year Warranty

More information on the general DEWALT warranty

D55153 Includes:

- DEWALT® Compressor Oil