



D55154

1.1 HP Continuous 4 Gallon Electric Wheeled Dolly-Style Air Compressor with Panel

Product Features

- 4.0 CFM delivered at 90 PSI pump provides rapid recovery
- Oil lubricated pump improves durability
- Cast iron cylinder enhances pump life
- 10" pneumatic wheel and handle kit for ease of mobility
- Top load panel with positioning holes allows unit to transport loads up to 100 lbs
- High-flow regulator for increased performance
- Run multiple tools from dual universal quick couplers
- Ball valve drain allows for quick and thorough tank draining
- Convenient cord wrap for easy storage
- Dual soft start valves assist in cold weather start-up



Specifications

Horsepower	1.1HP
Drive	Direct
Tank Size	4gal
Power Supply	120V AC, 15 amps, 60 Hz, 2 pole induction motor
CFM @ 100 PSI	3.8CFM
Pump Speed	3,400rpm
Tool Length	22.0"
Tool Width	18.5"
Tool Height	23.0"
Tool Weight	87lbs
Shipping Weight	95lbs

Warranty Information

This DEWALT® High Performance Industrial Tool comes with a warranty package that includes:

- 30 Day Money Back Guarantee
- 1 Year Free Service Contract
- 1 Year Warranty

More information on the general DEWALT warranty

D55154 Includes:

- DEWALT® Compressor Oil
- control panel with (2) universal quick couplers