

DEWALT**POWER TOOLS****HAMMER DRILLS**

1/2" VSR Dual Range Hammerdrill



1/2" VSR Single Speed Hammerdrill



1/2" VSR Pistol Grip Hammerdrill



1/2" VSR Pistol Grip Hammerdrill Kit



1/2" VSR Mid-Handle Grip Hammerdrill Kit

SPECIFICATIONS	DW505	DWS11	DWD520	DWDS20K	DWDS25K
Amps	7.8 Amps	7.8 Amps	10.0 Amps	10.0 Amps	10.0 Amps
Max Watts Out	650 W	650 W	980 W	980 W	980 W
No Load Speed	0-1,100 / 0-2,700 rpm	0-2,700 rpm	0-1,200 / 0-3,500 rpm	0-1,200 / 0-3,500 rpm	0-1,200 / 0-3,500 rpm
Blows/Min	0-19,000 / 0-46,000 bpm	0-46,000 bpm	0-56,000 bpm	0-56,000 bpm	0-56,000 bpm
Capacity In Steel	1/2"	1/2"	1/2"	1/2"	1/2"
Capacity In Wood	1-1/2"	1-1/4"	1-1/2"	1-1/2"	1-1/2"
Concrete Optimum	5/32" - 3/8"	5/32" - 3/8"	5/32" - 7/16"	5/32" - 7/16"	5/32" - 7/16"
Kit Box	No	No	No	Yes	Yes
Tool Length	13"	11-1/2"	14"	14"	13"
Tool Weight	4.8 lbs	4.3 lbs	6.0 lbs	6.0 lbs	6.0 lbs

CORDLESS SDS ROTARY HAMMERS

18V 7/8" (22mm) Cordless SDS Hammer Kit



20V MAX* Lithium Ion 3 Mode SDS Rotary Hammer Kit (3.0 Ah)



24V 7/8" (22mm) Cordless SDS Hammer Kit

SPECIFICATIONS	DC212KA	DCH213L2	DC223KA
Volts	18V	20V MAX*	24V
Chuck Type	SDS Plus	SDS Plus	SDS Plus
No Load Speed	0-1,100 rpm	0-1,100 rpm	0-1,100 rpm
Blows/Min	0-4,100 bpm	0-4,100 bpm	0-4,100 bpm
Impact Energy	1.7 ft-lbs	1.7 ft-lbs	1.7 ft-lbs
Vibration Measurement	8.0 m/s ²	6.9 m/s ²	9.0 m/s ²
Vibration Control	Yes - SHOCKS™	Yes - SHOCKS™	Yes - SHOCKS™
Chipping	No	Yes	Yes
Concrete Optimum	5/32 - 1/2"	5/32 - 1/2"	5/32 - 1/2"
Weight	7.6 lbs	6.4 lbs	8.4 lbs
Charger/Batteries	1 Hour Charger / (2) 18V XRP™	Fast charger / (2) 20V MAX* (3.0 Ah)	1 Hour Charger / (2) 24V
Includes	360° side handle with depth rod	360° side handle with depth rod	360° side handle with depth rod
Also available	DC212KL (with 1 Hour Charger (2) 18V XRP™ Li-Ion); DC212B (Tool Only)	-	DC233KL (with 1 Hour Charger (2) 36V batteries); DC233KLDH (with 1 Hour Charger / (2) 36V batteries, D25302DH Dust extraction system)

SDS ROTARY HAMMERS

7/8" Pistol Grip SDS Rotary Hammerdrill



7/8" D-Handle SDS Rotary Hammerdrill



1" Pistol Grip 3-Mode SDS Rotary Hammerdrill



1" D-Handle 3-Mode SDS Hammerdrill



1" D-Handle SDS Rotary Hammerdrill

SPECIFICATIONS	D25012K	D25023K	D25123K	D25213K	D25223K
Optimal Concrete Drilling	5/32" - 1/2"	5/32" - 1/2"	5/32" - 5/8"	5/32" - 5/8"	5/32" - 5/8"
Amps	6.0 Amps	6.9 Amps	8.0 Amps	8.0 Amps	8.0 Amps
Impact Energy	1.8 ft-lbs	1.8 ft-lbs	2.5 ft-lbs	2.5 ft-lbs	2.5 ft-lbs
Vibration Control	No	No	No	No	Yes - SHOCKS®
No Load Speed	0-1,550 rpm	0-1,550 rpm	0-1,150 rpm	0-1,150 rpm	0-1,150 rpm
Blows/Min	0-4,150 bpm	0-4,550 bpm	0-4,300 bpm	0-4,300 bpm	0-4,300 bpm
Vibration Measurement	11.0 m/s ²	13.2 m/s ²	17.8 m/s ²	21.0 m/s ²	10.0 m/s ²
Chipping	No	Yes	Yes	Yes	Yes
Clutch	Yes	Yes	Yes	Yes	Yes
Tool Length	13.2"	16.2"	14.2"	16.6"	17.7"
Tool Weight	5.2 lbs	5.5 lbs	5.7 lbs	6.1 lbs	7.0 lbs
Warranty - Service Contract	1 Yr.	1 Yr.	1 Yr.	1 Yr.	2 Yr.