



CORDLESS POWER TOOLS

GUARANTEED TOUGH.

SCREWDRIVERS



SPECIFICATIONS	DC520KA	DCF61052	DW920K-2
Volts	18V	12V MAX*	7.2V
Drive Size	1/4"	1/4"	1/4" Hex
No Load Speed	0-900 / 0-2,900 rpm	0-1,050 rpm	0-500 rpm
Chuck	-	1-Handed Loading, 1/4" Hex Chuck	-
Max Torque (#-lbs)	180 in.-lbs	-	80 in.-lbs
Max Power	-	160 UAW0	-
Capacity (CRS)	12 gauge	-	-
LEDs	-	3	-
length	-	6-1/4"	-
Weight	5.1 lbs	2.2 lbs	3.5 lbs
Charger/Batteries	1 Hour Charger / (2) 18V XRP™	1hrst Charger / (2) 12V MAX*	1 Hour Charger / (2) 7.2V
Includes	B1 lip / magnetic holder, drywall nosepiece, & TEKS® nosepiece	(1) B1 lip & (1) belt hook	-

SDS ROTARY HAMMERS



SPECIFICATIONS	DC212B	DC212KA	DC212KL
Volts	18V	18V	18V
Chuck Type	SDS Plus	SDS Plus	SDS Plus
No Load Speed	0-1,100 rpm	0-1,100 rpm	0-1,100 rpm
Blows/Min	0-4,100 bpm	0-4,100 bpm	0-4,100 bpm
Impact Energy	1.7 ft.-lbs	1.7 ft.-lbs	1.7 ft.-lbs
Vibration Measurement	8.0 m/s ²	8.0 m/s ²	8.0 m/s ²
Vibration Control	Yes - SHOCKS™	Yes - SHOCKS™	Yes - SHOCKS™
Chipping	No	No	No
Concrete Optimum	5/32 - 1/2"	5/32 - 1/2"	5/32 - 1/2"
Weight	5.25 lbs	7.6 lbs	6.7 lbs
Charger/Batteries	Sold Separately	1 Hour Charger / (2) 18V XRP™	1 Hour Charger / (2) 18V XRP™ Li-Ion
Includes	360° side handle with depth rod	360° side handle with depth rod	360° side handle with depth rod



SPECIFICATIONS	DCH213L2	DC223KA	DC233KL	DC233KLDH
Volts	20V MAX*	24V	36V	36V
Chuck Type	SDS Plus	SDS Plus	SDS Plus	SDS Plus
No Load Speed	0-1,100 rpm	0-1,100 rpm	1,150 rpm	1,150 rpm
Blows/Min	0-4,100 bpm	0-4,100 bpm	0-4,400 bpm	0-4,400 bpm
Impact Energy	1.7 ft.-lbs	1.7 ft.-lbs	1.9 ft.-lbs	1.9 ft.-lbs
Vibration Measurement	8.0 m/s ²	9.0 m/s ²	8.5 m/s ²	8.5 m/s ²
Vibration Control	Yes - SHOCKS™	Yes - SHOCKS™	Yes - SHOCKS™	Yes
Chipping	Yes	Yes	Yes	Yes
Concrete Optimum	5/32 - 1/2"	5/32 - 1/2"	5/32" - 5/8"	5/32" - 5/8"
Weight	6.4 lbs	8.4 lbs	7.8 lbs	7.8 lbs
Charger/Batteries	Fast charger / (2) 20V MAX* (3.0 Ah)	1 Hour Charger / (2) 24V	1 Hour Charger / (2) 36V	1 Hour Charger / (2) 36V
Includes	360° side handle with depth rod	360° side handle with depth rod	360° side handle with depth rod	D25302DH dust extraction system, and 360° side handle with depth rod