



**HEAVY-DUTY POWER TOOLS**

**GUARANTEED TOUGH.**



**RECIPROCATING SAWS**

36V Cordless Reciprocating Saw Kit    18V Cordless Reciprocating Saw Kit    14.4V Cordless Reciprocating Saw Kit

SPECIFICATIONS	DC305K	DC385K	DW937K
Voltage	36V	18V	14.4V
Keyless Blade Clamp	Yes	Yes	Yes
Strokes/Min	0-3,000 spm	0-3,000 spm	0-2,700 spm
4 Position Blade Clamp	Yes	Yes	No
Stroke Length	1-1/8"	1-1/8"	7/8"
Electric Brake	Yes	Yes	Yes
Tool Weight	8.4 lbs	8.3 lbs	6 lbs
Charger/Batteries	1 hour / (1) 36V	1 hour / (1) 18V XRP™	1 hour / (1) 14.4V
Includes	reciprocating saw blade	reciprocating saw blade	reciprocating saw blade



**PENCIL VIBRATOR**

18V Cordless Pencil Vibrator Kit

SPECIFICATIONS	DC530KA
Voltage	18V
Vibrator Diameter	1-1/8"
Shaft Length	4'
Vibrations Per Minute	14,000 vpm
Charger/Batteries	1 hour / (2) 18V XRP™
Includes	soft-side bag for batteries and charger



**SDS HAMMERS**

36V Cordless 1" SDS Rotary Hammer Kit    24V Cordless 7/8" SDS Hammer Kit    18V Cordless 7/8" SDS Hammer Kit

SPECIFICATIONS	DC233KL	DC223KA	DC212KA
Voltage	36V	24V	18V
No Load Speed	0-1,150 rpm	0-1,100 rpm	0-1,100 rpm
Blows/Min	0-4,400 bpm	0-4,100 bpm	0-4,100 bpm
Concrete Maximum	1"	7/8"	7/8"
Concrete Optimum	1/4"-5/8"	5/32"-1/2"	5/32"-1/2"
Tool Length	10.5"	10.5"	10.5"
Tool Weight	7.8 lbs	8.4 lbs	7.6 lbs
Charger/Batteries	1 hour / (2) 36V	1 hour / (2) 24V	1 hour / (2) 18V XRP™
Includes	360° side handle, depth rod	360° side handle, depth rod	360° side handle, depth rod



**JIG SAWS**

36V Cordless Jig Saw Kit w/Keyless Blade Change    18V Cordless Jig Saw Kit w/Keyless Blade Change

SPECIFICATIONS	DC308K	DC330K
Voltage	36V	18V
Strokes/Min	0-2,700 spm	0-3,000 spm
Stroke Length	1"	1"
Keyless Blade Clamp	Yes	Yes
Dust Blower	Yes	Yes
Tool Weight	7.5 lbs	7.5 lbs
Charger/Batteries	1 hour / (1) 36V	1 hour / (1) 18V XRP™
Includes	jig saw blade	jig saw blade



**CUT-OUT TOOLS**

18V Cordless Cut-Out Tool    14.4V Cordless Cut-Out Tool

SPECIFICATIONS	DC530KA	DC551KA
Voltage	18V	14.4V
No Load Speed	26,000 rpm	26,000 rpm
Collet Diameter	1/4", 1/8"	1/4", 1/8"
Adjustable Guide	Yes	Yes
Tool Weight	4.5 lbs	4.2 lbs
Charger/Batteries	1 hour / (2) 18V XRP™	1 hour / (2) 14.4V XRP™
Includes	1 general purpose bit, 1 drywall cutting bit, 1/4" & 1/8" collets	1 general purpose bit, 1 drywall cutting bit, 1/4" & 1/8" collets



**SCREWDRIVERS**

18V Cordless Light Gauge Steel Framing Screwdriver    18V Cordless Drywall/Deck Screwdriver Kit    12V Cordless Drywall/Deck Screwdriver Kit    1/4" (6mm) 7.2V Cordless Two-Position Screwdriver Kit

SPECIFICATIONS	DC668KA	DC520KA	DW979K-2	DW920K-2
Voltage	18V	18V	12V	7.2V
Drive	1/4" hex	1/4" Hex	1/4" Hex	1/4" Hex
No Load Speed	0-900/0-2,700 rpm	0-900/0-2,900 rpm	0-800/0-2,300 rpm	0-500 rpm
Max. Torque	180 in-lbs	180 in-lbs	180 in-lbs	80 in-lbs
Capacity (CRS)	12-28 ga.	12 ga.	12 ga.	-
Tool Weight	5.4 lbs	5.1 lbs	4.2 lbs	2.5 lbs
Charger/Batteries	1 hour / (2) 18V XRP™	1 hour / (2) 18V XRP™	1 hour / (2) 12V	1 hour / (2) 7.2V
Includes	#2 Phillips screwdriver bit, 5/16" nut runner	bit tip/magnetic holder, drywall nosepiece, TEKS® nosepiece	bit tip/magnetic holder, drywall nosepiece, TEKS® nosepiece	(2) screwdriver bits

www.DeWALT.com

1-800-4 DEWALT

<PREVIOUS

3 NEXT>