



CORDLESS POWER TOOLS

GUARANTEED TOUGH.

CIRCULAR SAWS



SPECIFICATIONS	DC300K	DCS391L1	DCS391B
Volts	36V	20V MAX*	20V MAX*
No Load Speed	4,000 rpm	3,700 rpm	3,700 rpm
Blade Diameter	7-1/4"	6-1/2"	6-1/2"
Bevel Capacity	0° - 50°	0° - 50°	0° - 50°
Depth of Cut at 45°	1-5/8"	1-5/8"	1-5/8"
Depth of Cut at 90°	2-7/16"	2-1/4"	2-1/4"
Weight	9.9 lbs	8.0 lbs	8.0 lbs
Charger/Batteries	1 Hour Charger / (1) 36V	Fast Charger, (1) 20V MAX* Lithium Ion 3.0 Ah	Sold Separately
Includes	7-1/4" carbide tipped blade	Carbide tipped circular sawblade	Carbide tipped circular sawblade



SPECIFICATIONS	DCS390L	DCS390K	DCS390B
Volts	18V	18V	18V
No Load Speed	3,700 rpm	3,700 rpm	3,700 rpm
Blade Diameter	6-1/2"	6-1/2"	6-1/2"
Bevel Capacity	0° - 50°	0° - 50°	0° - 50°
Depth of Cut at 45°	1 - 5/8"	1 - 5/8"	1 - 5/8"
Depth of Cut at 90°	2-1/4"	2-1/4"	2-1/4"
Weight	7.8 lbs	8.7 lbs	6.3 lbs (tool only)
Charger/Batteries	1 Hour Charger / (1) 18V XRP™ Li-Ion	1 Hour Charger / (1) 18V XRP™	Sold Separately
Includes	6 - 1/2" 16 tooth carbide tipped blade, blade wrench	6 - 1/2" 16 tooth carbide tipped blade, blade wrench	6-1/2" 16 tooth carbide saw blade, blade wrench

DCS391L1

Powerful 480 MWO, 3700 RPM Motor
Delivers power and speed to make the most demanding cuts with ease

High Strength and Lightweight Magnesium Shoe
Provides jobsite durability for long-term cut accuracy



Optimized Rubber Overmolded Comfort Grip
Delivers optimal balance and control



JIG SAWS



SPECIFICATIONS	DCS330L	DC330K	DC330B
Volts	18V	18V	18V
Strokes/Min	0,3,000 spm	0,3,000 spm	0,3,000 spm
Stroke Length	1"	1"	1"
Keyless Blade Clamp	Yes	Yes	Yes
Dust Blower	Yes	Yes	Yes
Weight	6.6 lbs	7.5 lbs	5.1 lbs (tool only)
Charger/Batteries	1 Hour Charger / (1) 18V XRP™ Li-Ion	1 Hour Charger / (1) 18V XRP™	Sold Separately
Includes	Jig saw blade	Jig saw blade	-

1-800-4DEWALT

CORDLESS POWER TOOLS 11