



HEAVY-DUTY POWER TOOLS

GUARANTEED TOUGH.



RECIPROCATING SAWS

36V Cordless Reciprocating Saw Kit 18V Cordless Reciprocating Saw Kit 14.4V Cordless Reciprocating Saw Kit

SPECIFICATIONS	DC305K	DC385K	DW937K
Voltage	36V	18V	14.4V
Keyless Blade Clamp	Yes	Yes	Yes
Strokes/Min	0-3,000 spm	0-3,000 spm	0-2,700 spm
4 Position Blade Clamp	Yes	Yes	No
Stroke Length	1-1/8"	1-1/8"	7/8"
Electric Brake	Yes	Yes	Yes
Tool Weight	8.4 lbs	8.3 lbs	6 lbs
Charger/Batteries	1 hour / (1) 36V	1 hour / (1) 18V XRP™	1 hour / (1) 14.4V
Includes	reciprocating saw blade	reciprocating saw blade	reciprocating saw blade



PENCIL VIBRATOR

18V Cordless Pencil Vibrator Kit

SPECIFICATIONS	DC530KA
Voltage	18V
Vibrator Diameter	1-1/8"
Shaft Length	4'
Vibrations Per Minute	14,000 vpm
Charger/Batteries	1 hour / (2) 18V XRP™
Includes	soft-side bag for batteries and charger



SDS HAMMERS

36V Cordless 1" SDS Rotary Hammer Kit 24V Cordless 7/8" SDS Hammer Kit 18V Cordless 7/8" SDS Hammer Kit

SPECIFICATIONS	DC233KL	DC223KA	DC212KA
Voltage	36V	24V	18V
No Load Speed	0-1,150 rpm	0-1,100 rpm	0-1,100 rpm
Blows/Min	0-4,400 bpm	0-4,100 bpm	0-4,100 bpm
Concrete Maximum	1"	7/8"	7/8"
Concrete Optimum	1/4"-5/8"	5/32"-1/2"	5/32"-1/2"
Tool Length	10.5"	10.5"	10.5"
Tool Weight	7.8 lbs	8.4 lbs	7.6 lbs
Charger/Batteries	1 hour / (2) 36V	1 hour / (2) 24V	1 hour / (2) 18V XRP™
Includes	360° side handle, depth rod	360° side handle, depth rod	360° side handle, depth rod



JIG SAWS

36V Cordless Jig Saw Kit w/Keyless Blade Change 18V Cordless Jig Saw Kit w/Keyless Blade Change

SPECIFICATIONS	DC308K	DC330K
Voltage	36V	18V
Strokes/Min	0-2,700 spm	0-3,000 spm
Stroke Length	1"	1"
Keyless Blade Clamp	Yes	Yes
Dust Blower	Yes	Yes
Tool Weight	7.5 lbs	7.5 lbs
Charger/Batteries	1 hour / (1) 36V	1 hour / (1) 18V XRP™
Includes	jig saw blade	jig saw blade



CUT-OUT TOOLS

18V Cordless Cut-Out Tool 14.4V Cordless Cut-Out Tool

SPECIFICATIONS	DC530KA	DC551KA
Voltage	18V	14.4V
No Load Speed	26,000 rpm	26,000 rpm
Collet Diameter	1/4", 1/8"	1/4", 1/8"
Adjustable Guide	Yes	Yes
Tool Weight	4.5 lbs	4.2 lbs
Charger/Batteries	1 hour / (2) 18V XRP™	1 hour / (2) 14.4V XRP™
Includes	1 general purpose bit, 1 drywall cutting bit, 1/4" & 1/8" collets	1 general purpose bit, 1 drywall cutting bit, 1/4" & 1/8" collets



SCREWDRIVERS

18V Cordless Light Gauge Steel Framing Screwdriver 18V Cordless Drywall/Deck Screwdriver Kit 12V Cordless Drywall/Deck Screwdriver Kit 1/4" (6mm) 7.2V Cordless Two-Position Screwdriver Kit

SPECIFICATIONS	DC668KA	DC520KA	DW979K-2	DW920K-2
Voltage	18V	18V	12V	7.2V
Drive	1/4" hex	1/4" Hex	1/4" Hex	1/4" Hex
No Load Speed	0-900/0-2,700 rpm	0-900/0-2,900 rpm	0-800/0-2,300 rpm	0-500 rpm
Max. Torque	180 in-lbs	180 in-lbs	180 in-lbs	80 in-lbs
Capacity (CRS)	12-28 ga.	12 ga.	12 ga.	-
Tool Weight	5.4 lbs	5.1 lbs	4.2 lbs	2.5 lbs
Charger/Batteries	1 hour / (2) 18V XRP™	1 hour / (2) 18V XRP™	1 hour / (2) 12V	1 hour / (2) 7.2V
Includes	#2 Phillips screwdriver bit, 5/16" nut runner	bit tip/magnetic holder, drywall nosepiece, TEKS® nosepiece	bit tip/magnetic holder, drywall nosepiece, TEKS® nosepiece	(2) screwdriver bits

www.DeWALT.com

1-800-4 DEWALT

< PREVIOUS

3 NEXT >