



CORDLESS POWER TOOLS

GUARANTEED TOUGH.



DCB200
20V MAX* (3.0Ah)



DCB201
20V MAX* (1.5Ah)



DCB120
12V MAX*



12V MAX*
Fast Charger



12V MAX* - 20V MAX*
Lithium Ion Battery Charger



12V MAX* - 20V MAX*
Lithium Ion Battery Charger



12V MAX* - 20V MAX* 7.2V - 18V
Dual System, Dual Port Charger

12V & 20V MAX* CHARGERS

SPECIFICATIONS	DCB100	DCB101	DCB119	DCB103
DCB120 12V MAX*	40	30	45	45
DCB200 20V MAX*	X	60	90	60
DCB200-2 20V MAX*	X	60	90	60
DCB201 20V MAX*	X	30	45	30
DCB201-2 20V MAX*	X	30	45	30



DC9091
14.4V



DC9360
36V



DC9144
14.4V



DW0242
24V



DC9071
12V



DC9096
18V



DW9061
9.6V



DC9180
18V



DW9057
7.2V

BATTERIES/CHARGERS

X=Not Compatible

SPECS

	DW9117 15 Minute Charger	DW0246 1 Hour Fan Cooled Charger	DW0249 1 Hour Fan Cooled Vehicle Charger	DC9000 1 Hour Charger	DC9310 NiCd/NiMH-U-Ion 1 Hour Charger	DC9319 1 Hour Vehicle Charger	DC9320 Dual Port 1 Hour Charger	DC912 Worksite Charger/Radio	DCB103 12V MAX* - 20V MAX* & 7.2V - 18V Dual System, Dual Port Charger
DC9360 36V	X	X	X	60	X	X	X	X	X
DW0242 24V	X	60	60	X	X	X	X	X	X
DC9096 18V	20	X	X	X	60	60	60	60	60
DC9180 18V	X	X	X	X	60	60	60	60	60
DC9144 14.4V	X	X	X	X	60	60	60	60	60
DC9091 14.4V	20	X	X	X	60	60	60	60	60
DC9071 12V	20	X	X	X	60	60	60	60	60
DW9061 9.6V	15	X	X	X	45	45	45	45	45
DW9057 7.2V	12	X	X	X	30	30	30	30	30

1-800-4DEWALT

CORDLESS POWER TOOLS 21