



CORDLESS POWER TOOLS

GUARANTEED TOUGH.

DRILL/DRIVERS



20V MAX* Lithium Ion Premium 3-Speed Drill/Driver Kit (3.0Ah)



20V MAX* Lithium Ion Compact Drill/Driver Kit (1.5Ah)



18V 1/2" (13mm) Cordless XRPTM Drill/Driver Kit



18V 1/2" (13mm) Cordless XRPTM Drill/Driver Kit

SPECIFICATIONS	DCD980L2	DCD780C2	DCD940KX	DCD960KL
Volts	20V MAX*	20V MAX*	18V	18V
Max Power	535 UWO	350 UWO	450 UWO	450 UWO
# of Speed Settings	3	2	3	3
No Load Speed	-	0-600/0-2,000 rpm	-	-
Max RPM	0-575/0-1,350/0-2,000 rpm	2,000 rpm	0-500/0-1,250/0-2,000 rpm	0-500/0-1,250/0-2,000 rpm
Chuck Size	1/2"	1/2"	1/2"	1/2"
Chuck Type	Metal, ratcheting	Ratcheting	Metal, ratcheting	Metal, ratcheting
Weight	5.2 lbs	3.4 lbs	6.25 lbs	5.25 lbs
Charger/Batteries	1 Hour Charger / (2) 20V MAX* Lithium Ion 3.0Ah	30 Minute Fast Charger / (2) 20V MAX* Lithium Ion 1.5Ah	1 Hour Charger / (2) 18V XRPTM	1 Hour NiCd/NiMH/Li-Ion Charger / (2) 18V XRPTM Li-Ion
Includes	360° side handle	On-board bit holder & belt hook	360° side handle	360° side handle



18V 1/2" (13mm) Cordless Compact Li-Ion Drill/Driver Kit



1/2" (13mm) 18V Cordless Compact Drill/Driver (Tool Only)



1/2" (13mm) 18V Cordless Compact Drill/Driver Kit



1/2" (13mm) 14.4V Cordless Drill/Driver Kit

SPECIFICATIONS	DCD760KL	DCD760B	DC720KA	DCD920KX
Volts	18V	18V	18V	14.4V
Max Power	350 UWO	350 UWO	410 UWO	325 UWO
# of Speed Settings	2	2	2	3
Max RPM	0-500/0-1,700 rpm	0-500/0-1,700 rpm	0-500/0-1,700 rpm	0-425/0-1,200/0-1,800 rpm
Chuck Size	1/2"	1/2"	1/2"	1/2"
Chuck Type	Plastic, ratcheting	Plastic, ratcheting	Plastic, ratcheting	Metal, ratcheting
Weight	4.0 lbs	3.0 lbs (tool only)	4.8 lbs	5.75 lbs
Charger/Batteries	30 Minute Charger, (2) 18V Compact Li-Ion	Sold Separately	1 Hour Charger / (2) 18V	1 Hour Charger / (2) 14.4V XRPTM



1/2" (13mm) 14.4V Cordless Compact Drill/Driver Kit



12V MAX* 3/8" Drill/Driver Kit



12V 1/2" (13mm) Cordless XRPTM Drill/Driver Kit



12V 1/2" (13mm) Cordless Compact Drill/Driver Kit

SPECIFICATIONS	DC730KA	DCD710S2	DCD910KX	DC742KA/VA*
Volts	14.4V	12V MAX*	12V	12V
Max Power	300 UWO	189 UWO	285 UWO	200 UWO
Max RPM	0-400/0-1,450 rpm	0-400/0-1,500 rpm	0-425/0-1,200/0-1,800 rpm	0-400/0-1,450 rpm
Chuck Size	1/2"	3/8"	1/2"	3/8"
Chuck Type	Plastic, ratcheting	Single sleeve	Metal, ratcheting	Plastic, ratcheting
Weight	4.3 lbs	2.4 lbs	5.25 lbs	3.8 lbs
Charger/Batteries	1 Hour Charger / (2) 14.4V	Fast Charger, (2) 12V MAX* Lithium Ion (1) belt hook	1 Hour Charger / (2) 12V XRPTM	Fast Charger / (2) 12V
Includes	-	-	-	-



3/8" (10mm) 9.6V Cordless Compact Drill/Driver Kit

SPECIFICATIONS	DC750KA
Volts	9.6V
Max Power	130 UWO
# of Speed Settings	2
Max RPM	0-300/0-1,100 rpm
Chuck Size	3/8"
Chuck Type	Plastic, ratcheting
Weight	3.4 lbs
Charger/Batteries	1 Hour Charger / (2) 9.6V
Includes	-

COMPACT

Short Length of 8.2" Compact to fit into tight spaces

Single Sleeve 1/2" Chuck Reduces bit slippage during high torque application

Bright L.E.D. Worklight Increased productivity in dark areas

18V Battery Pack Small and lightweight battery for increased comfort



Increased Performance Delivers maximum power (UWO) during drilling and fastening applications

Improved Handle Design Delivers increased comfort and provides less user fatigue

1-800-4DEWALT

CORDLESS POWER TOOLS 5