



CORDLESS POWER TOOLS

GUARANTEED TOUGH.

DRILL/DRIVERS



20V MAX* Lithium Ion Premium 3-Speed Drill/Driver Kit (3.0Ah)



20V MAX* Lithium Ion Compact Drill/Driver Kit (1.5Ah)



18V 1/2" (13mm) Cordless XRPT™ Drill/Driver Kit



18V 1/2" (13mm) Cordless XRPT™ Drill/Driver Kit

SPECIFICATIONS	DCD980L2	DCD780C2	DCD940KX	DCD960KL
Volts	20V MAX*	20V MAX*	18V	18V
Max Power	535 UWO	350 UWO	450 UWO	450 UWO
# of Speed Settings	3	2	3	3
No Load Speed	-	0-600/0-2,000 rpm	-	-
Max RPM	0-575/0-1,350/0-2,000 rpm	2,000 rpm	0-500/0-1,250/0-2,000 rpm	0-500/0-1,250/0-2,000 rpm
Chuck Size	1/2"	1/2"	1/2"	1/2"
Chuck Type	Metal, ratcheting	Ratcheting	Metal, ratcheting	Metal, ratcheting
Weight	5.2 lbs	3.4 lbs	6.25 lbs	5.25 lbs
Charger/Batteries	1 Hour Charger / (2) 20V MAX* Lithium Ion 3.0Ah	30 Minute Fast Charger / (2) 20V MAX* Lithium Ion 1.5Ah	1 Hour Charger / (2) 18V XRPT™	1 Hour NiCd/NiMH/Li-Ion Charger / (2) 18V XRPT™ Li-Ion
Includes	360° side handle	On-board bit holder & belt hook	360° side handle	360° side handle



18V 1/2" (13mm) Cordless Compact Li-Ion Drill/Driver Kit



1/2" (13mm) 18V Cordless Compact Drill/Driver (Tool Only)



1/2" (13mm) 18V Cordless Compact Drill/Driver Kit



1/2" (13mm) 14.4V Cordless Drill/Driver Kit

SPECIFICATIONS	DCD760KL	DCD760B	DC720KA	DCD920KX
Volts	18V	18V	18V	14.4V
Max Power	350 UWO	350 UWO	410 UWO	325 UWO
# of Speed Settings	2	2	2	3
Max RPM	0-500/0-1,700 rpm	0-500/0-1,700 rpm	0-500/0-1,700 rpm	0-425/0-1,200/0-1,800 rpm
Chuck Size	1/2"	1/2"	1/2"	1/2"
Chuck Type	Plastic, ratcheting	Plastic, ratcheting	Plastic, ratcheting	Metal, ratcheting
Weight	4.0 lbs	3.0 lbs (tool only)	4.8 lbs	5.75 lbs
Charger/Batteries	30 Minute Charger, (2) 18V Compact Li-Ion	Sold Separately	1 Hour Charger / (2) 18V	1 Hour Charger / (2) 14.4V XRPT™



1/2" (13mm) 14.4V Cordless Compact Drill/Driver Kit



12V MAX* 3/8" Drill/Driver Kit



12V 1/2" (13mm) Cordless XRPT™ Drill/Driver Kit



12V 1/2" (13mm) Cordless Compact Drill/Driver Kit

SPECIFICATIONS	DC730KA	DCD710S2	DCD910KX	DC742KA/VA*
Volts	14.4V	12V MAX*	12V	12V
Max Power	300 UWO	189 UWO	285 UWO	200 UWO
Max RPM	0-400/0-1,450 rpm	0-400/0-1,500 rpm	0-425/0-1,200/0-1,800 rpm	0-400/0-1,450 rpm
Chuck Size	1/2"	3/8"	1/2"	3/8"
Chuck Type	Plastic, ratcheting	Single sleeve	Metal, ratcheting	Plastic, ratcheting
Weight	4.3 lbs	2.4 lbs	5.25 lbs	3.8 lbs
Charger/Batteries	1 Hour Charger / (2) 14.4V	Fast Charger, (2) 12V MAX* Lithium Ion (1) belt hook	1 Hour Charger / (2) 12V XRPT™	Fast Charger / (2) 12V
Includes	-	-	-	-



3/8" (10mm) 9.6V Cordless Compact Drill/Driver Kit

SPECIFICATIONS	DC750KA
Volts	9.6V
Max Power	130 UWO
# of Speed Settings	2
Max RPM	0-300/0-1,100 rpm
Chuck Size	3/8"
Chuck Type	Plastic, ratcheting
Weight	3.4 lbs
Charger/Batteries	1 Hour Charger / (2) 9.6V
Includes	-

COMPACT

- Single Sleeve 1/2" Chuck**
Reduces bit slippage during high torque application
- Bright L.E.D. Worklight**
Increased productivity in dark areas
- 18V Battery Pack**
Small and lightweight battery for increased comfort



1-800-4DEWALT