



# CORDLESS POWER TOOLS

**GUARANTEED TOUGH.**

**IMPACT DRIVERS & WRENCHES**



20V MAX\* Lithium Ion 1/4" Impact Driver Kit (3.0Ah)



20V MAX\* Lithium Ion 1/4" Impact Driver Kit (1.5Ah)



20V MAX\* Lithium Ion 1/4" Impact Driver (Tool Only)

SPECIFICATIONS	DCF885L2	DCF885C2	DCF885B
Volts	20V MAX*	20V MAX*	20V MAX*
Drive Size	1/4"	1/4"	1/4"
No Load Speed	2,800 rpm	2,800 rpm	2,800 rpm
Impacts/Min	3,200 ipm	3,200 ipm	3,200 ipm
Torque (ft-lbs)	1,400 in-lbs	1,400 in-lbs	1,400 in-lbs
Torque (ft-lbs)	117 ft-lbs	117 ft-lbs	117 ft-lbs
Tool Length	5.55"	5.55"	5.55"
Weight	3.4 lbs	2.8 lbs	2.0 lbs (tool only)
Charger/Batteries	Fast Charger / (2) 20V MAX* Lithium Ion 3.0Ah	Fast Charger / (2) 20V MAX* Lithium Ion 1.5Ah	Sold Separately
Includes	Bel hook	Bel hook	Bel hook



18V Cordless Li-Ion Impact Driver Kit



18V Cordless Li-Ion Impact Driver Kit



18V Cordless Impact Driver Kit



18V Cordless Impact Driver (Tool Only)

SPECIFICATIONS	DCS27KL	DCF826KL	DCS25KA	DCS25B
Volts	18V	18V	18V	18V
Drive Size	1/4" hex shank quick release	1/4" hex shank quick release	1/4" hex shank quick release	1/4" hex shank quick release
No Load Speed	0-2,400 rpm	0-2,400 rpm	0-2,400 rpm	0-2,400 rpm
Impacts/Min	0-2,700 ipm	0-2,700 ipm	0-2,700 ipm	0-2,700 ipm
Torque (ft-lbs)	1,330in-lbs	1,330in-lbs	1,330in-lbs	1,330in-lbs
Torque (ft-lbs)	111 ft-lbs	111 ft-lbs	111 ft-lbs	111 ft-lbs
Tool Length	5-3/4"	5-3/4"	5-3/4"	5-3/4"
Weight	3.7 lbs	3.1 lbs	4.6 lbs	2.2 lbs (tool only)
Charger/Batteries	1 Hour NiCd/NI-MH/Li-Ion Charger / (2) 18V XRP™ Li-Ion	30 Minute Charger / (2) 18V Compact Li-Ion	1 Hour Charger / (2) 18V XRP™	Sold Separately



1-800-4DEWALT

CORDLESS POWER TOOLS 7