

POWER, PNEUMATIC & HYDRAULIC TOOLS

COMBO TOOL KITS



adsinc.com/dewalt



A



B



HEAVY-DUTY 18V COMPACT CORDLESS™

- DC720 18V 1/2" compact drill/driver delivers 410 unit watts out of maximum power
- DW936 18V trim saw with 5-3/8" 16-tooth carbide blade and rip fence can cut a "2x4" in a single pass
- DW938 18V cordless reciprocating saw with keyless blade clamp allows for quick blade change without touching blade or reciprocating shaft
- DW908 18V pivoting head flashlight which allows light to be projected in any direction

Model	Item Number
Heavy-Duty 18V 4 Tool Combo Kit	DC4CKTA
18V 1/2" Compact Drill/Driver	DC720
18V Trim Saw	DW936
18V Cordless Reciprocating Saw	DW938
18V Pivoting Head Flashlight	DW908

18V CORDLESS XRP™ LI-ION

- DCD970 XRP™ 18V cordless hammerdrill with patented 3-speed all-metal transmission and 1/2" self-tightening chuck delivers 450 units watts out of maximum performance, faster application speed, and superior bit retention
- DC827 18V impact driver delivers 1,330 in.-lbs of torque and 0-2,400 RPMs offering power and speed to perform a wide range of fastening applications at faster speeds
- DC385 18V reciprocating saw with 4-position keyless blade clamp allows for quick blade change without touching blade or reciprocating shaft
- DW919 18V flexible floodlight provides hands-free use
- XRP™ Li-Ion extended run-time batteries provide superior ergonomics, long run-time & battery life

Model	Item Number
4-Tool Cordless Combo Kit	DCK47SL
18V Impact Driver	DC827
18V Reciprocating Saw	DC385
18V Flexible Floodlight	DW919

18V XRP LI-ION 6-TOOL COMBO KIT

- DCD970 18V XRP™ cordless hammerdrill with patented 3-speed all-metal transmission and 1/2" self-tightening chuck delivers 450 units watts out of maximum performance, faster application speed, and superior bit retention
- DC827 18V impact driver delivers 1,330 in.-lbs of torque and 0-2,400 rpm's offering power and speed to perform a wide range of fastening applications at faster speeds
- DC385 18V reciprocating saw with 4-position keyless blade clamp allows for quick blade change without touching blade or reciprocating shaft
- DC411 18V cut-off tool with 6,500 rpm provides high power for cutting and grinding applications
- DW059 18V 1/2" high torque impact wrench with 300 ft.-lbs of maximum torque
- DW919 18V flexible floodlight provides hands-free use
- XRP™ Li-Ion extended run-time batteries provide superior ergonomics, long run-time & battery life

Model	Item Number
18V Xrp Li-Ion 6-Tool Combo Kit	DCK675L