



## DCK555X

18V Cordless XRP™ 5-Tool Combo Kit

### Product Features

- DCD950 18V XRP™ cordless hammerdrill with patented 3-speed all-metal transmission and 1/2" metal ratcheting chuck with carbide inserts delivers 450 units watts out of maximum performance, faster application speed, and superior bit retention
- DC390 18V circular saw with 6-1/2" carbide blade can cut 2x4's at a 45° angle in a single pass
- DC385 18V cordless reciprocating saw with keyless blade clamp allows for quick blade change without touching blade or reciprocating shaft
- DC825 18V impact driver with 1,330 in-lbs of maximum torque
- DW919 18V flexible floodlight provides hands-free use

### Specifications

Voltage	18V
Number of tools in kit	5
Shipping Weight	36.0lbs

### Warranty Information

This DEWALT® High Performance Industrial Tool comes with a warranty package that includes:

- 90 Day Money Back Guarantee
- 1 Year Free Service Contract
- 3 Year Limited Warranty

[More information on the general DEWALT warranty](#)

### DCK555X Includes:

- DCD950 18V XRP™ 1/2" hammerdrill
- DC390 18V 6 1/2" circular saw
- DC385 18V reciprocating saw
- DC825 18V 1/4" impact driver
- DW919 18V flexible floodlight
- (2) 18V XRP™ batteries
- 1 hour charger
- 360° side handle
- carbide tipped blade
- contractor bag