

DeWalt DCS373L2 20V MAX Cordless Metal Cutting Circular Saw



Tech Specs:

- RPM: 3,700
- Blade Size: 5-1/2"
- Max Cut Depth: 1-11/16"
- Power: 460 Max Watts Out (MWO)

DCS373L2 includes:

- One (1) DeWalt DCS373 Li-Ion Metal Cutting Circular Saw
- Two (2) 20V MAX Li-Ion 3.0 Ah Fuel Gauge Battery Packs
- One (1) 5-1/2" Carbide Tipped Metal Cutting Blade
- One (1) Fast Charger
- One (1) Kit Box