



# CORDLESS POWER TOOLS

**GUARANTEED TOUGH.**



**DCB200**  
20V MAX\* (3.0Ah)



**DCB201**  
20V MAX\* (1.5Ah)



**DCB120**  
12V MAX\*



12V MAX\*  
Fast Charger



12V MAX\* - 20V MAX\*  
Lithium Ion Battery Charger



12V MAX\* - 20V MAX\*  
Lithium Ion Battery Charger



12V MAX\* - 20V MAX\* 7.2V - 18V  
Dual System, Dual Port Charger

**12V & 20V MAX\* CHARGERS**

SPECIFICATIONS	DCB100	DCB101	DCB119	DCB103
DCB120 12V MAX*	40	30	45	45
DCB200 20V MAX*	X	60	90	60
DCB200-2 20V MAX*	X	60	90	60
DCB201 20V MAX*	X	30	45	30
DCB201-2 20V MAX*	X	30	45	30



**DC9091**  
14.4V



**DC9360**  
36V



**DC9144**  
14.4V



**DW0242**  
24V



**DC9071**  
12V



**DC9096**  
18V



**DW9061**  
9.6V



**DC9180**  
18V



**DW9057**  
7.2V

**BATTERIES/CHARGERS**

X=Not Compatible

**SPECS**

	DW9117 15 Minute Charger	DW0246 1 Hour Fan Cooled Charger	DW0249 1 Hour Fan Cooled Vehicle Charger	DC9000 1 Hour Charger	DCB310 NiCd/NiMH-Ion 1 Hour Charger	DC9319 1 Hour Vehicle Charger	DCB320 Dual Port 1 Hour Charger	DC812 Worksite Charger/Radio	DCB103 12V MAX* - 20V MAX* & 7.2V - 18V Dual System, Dual Port Charger
DC9360 36V	X	X	X	60	X	X	X	X	X
DW0242 24V	X	60	60	X	X	X	X	X	X
DC9096 18V	20	X	X	X	60	60	60	60	60
DC9180 18V	X	X	X	X	60	60	60	60	60
DC9144 14.4V	X	X	X	X	60	60	60	60	60
DC9091 14.4V	20	X	X	X	60	60	60	60	60
DC9071 12V	20	X	X	X	60	60	60	60	60
DW9061 9.6V	15	X	X	X	45	45	45	45	45
DW9057 7.2V	12	X	X	X	30	30	30	30	30

1-800-4DEWALT

CORDLESS POWER TOOLS 21