



CORDLESS POWER TOOLS

GUARANTEED TOUGH.

HIGH TORQUE WRENCHES



1/2" (13mm) 36V Cordless Impact Wrench Kit



18V Cordless Impact Wrench Kit with Detent Pin Anvil



18V Cordless Impact Wrench with Detent Pin Anvil (Tool Only)



1/2" (13mm) 18V Cordless Li-Ion Impact Wrench Kit

SPECIFICATIONS	DC800KL	DC821KA	DC821B	DCF059KL
Volts	36V	18V	18V	18V
Drive Size	1/2" square w/ detent pin anvil	1/2" square w/ detent pin anvil	1/2" square w/ detent pin anvil	1/2" square w/ detent pin anvil
Max Torque	3,900in-lbs	1,920in-lbs	1,920in-lbs	3,600in-lbs
Max Torque	335 ft-lbs	160 ft-lbs	160 ft-lbs	300 ft-lbs
No Load Speed	1,400 rpm	0-2,100 rpm	0-2,100 rpm	0-1,650 rpm
Impacts/Minute	2,500 ipm	0-3,000 ipm	0-3,000 ipm	0-2,600 ipm
Switch	Rocker	-	-	-
Weight	7.5 lbs	5.3 lbs	2.9 lbs (tools only)	6.65 lbs
Tool Length	-	7-5/8"	7-5/8"	10-3/4"
Charger/Batteries	1 Hour Charger / (2) 36V	1 Hour Charger / (2) 18V XRP™	SoL Separately	1 Hour NiCd/NiMH/Li-Ion Charger / (2) 18V Li-Ion XRP™



1/2" (13mm) 18V Cordless High Torque Impact Wrench Kit with Hog Ring Anvil



1/2" (13mm) 18V Cordless High Torque Impact Wrench with Hog Ring Anvil (Tool Only)



1/2" (13mm) 18V Cordless High Torque Impact Wrench Kit with Detent Pin Anvil



1/2" (13mm) 18V Cordless High Torque Impact Wrench with Detent Pin Anvil (Tool Only)

SPECIFICATIONS	DW059HK-2	DW059HB	DW059K-2	DW059B
Volts	18V	18V	18V	18V
Drive Size	1/2" square w/hog ring anvil	1/2" square w/hog ring anvil	1/2" square w/detent pin anvil	1/2" square w/detent pin anvil
Max Torque	3,600in-lbs	3,600in-lbs	3,600in-lbs	3,600in-lbs
Max Torque	300 ft-lbs	300 ft-lbs	300 ft-lbs	300 ft-lbs
No Load Speed	1,650 rpm	1,650 rpm	1,650 rpm	1,650 rpm
Impacts/Minute	2,600 ipm	2,600 ipm	2,600 ipm	2,600 ipm
Weight	7.55 lbs	5.3 lbs (tool only)	7.55 lbs	5.3 lbs (tool only)
Tool Length	10-3/4"	10-3/4"	10-3/4"	10-3/4"
Charger/Batteries	1 Hour Charger / (2) 18V XRP™	SoL Separately	1 Hour Charger / (2) 18V XRP™	SoL Separately

RIGHT ANGLE DRILLS



20V MAX* Lithium Ion 3/8" Right Angle Drill/Driver Kit (1.5 Ah)

SPECIFICATIONS	DCD740C1
Volts	20V MAX*
Max Power	360 W/VO
Chuck Size	3/8"
# of Speed Settings	2
RPM	0-650/0-2,000 rpm
Chuck Type	Rastic, ratcheting
Weight	3.8 lbs
Charger/Batteries	Fast Charger / (1) 20V MAX* Lithium Ion 1.5Ah Battery
Includes	Bit hook, 2" Phillips bit tip

SCREWDRIVERS



18V Cordless Light Gauge Steel Framing Screwdriver Kit

SPECIFICATIONS	DC668KA
Volts	18V
Drive Size	1/4"
No Load Speed	0-900 / 0-2,700 rpm
Max Torque (ft-lbs)	180 ft-lbs
Capacity (CRS)	12-28 gauge
Weight	5.4 lbs
Charger/Batteries	1 Hour Charger / (2) 18V XRP™
Includes	#2 Phillips screwdriver bit, 5/16" nut driver

1-800-4DEWALT

CORDLESS POWER TOOLS 9