



HEAVY-DUTY POWER TOOLS

GUARANTEED TOUGH.

ROTARY LASERS



SPECIFICATIONS	DW077KI	DW077KD	DW077KDT	DW076KE
Power Supply	9.6V-18V DeWALT Batteries	9.6V-18V DeWALT Batteries	9.6V-18V DeWALT Batteries	9.6V-18V DeWALT Batteries
Accuracy per 100 ft.	1/8 in	1/8 in	1/8 in	1/8 in
Rotation Speed	0, 10, 60, 250, & 800 rpm	0, 10, 60, 250, & 800 rpm	0, 10, 60, 250, & 800 rpm	600 rpm
Self-Leveling Range	±5°	±5°	±5°	±5°
Indoor Visibility Range	200 (dia) ft	200 (dia) ft	200 (dia) ft	50 (dia) ft
Range with Detector	2000 (dia) ft	2000 (dia) ft	2000 (dia) ft	2000 (dia) ft
Laser Class	IIIa (<5mW) @ 635nm	IIIa (<5mW) @ 635nm	IIIa (<5mW) @ 635nm	IIIa (<5mW) @ 635nm
Tool Weight	5.5 lbs	5.5 lbs	5.5 lbs	5.5 lbs
Includes	1 hour charger, 18V battery, wall mount, wireless (IR) remote control, laser target card, laser enhancement glasses	same as DW077KI plus digital laser detector	same as DW077KI plus construction Tripod	1 hour charger, 14.4V battery, digital laser detector

ROTARY LASERS



SPECIFICATIONS	DW073K	DW073KD	DW071K	DW071KI	DW071KD
Power Supply	9.6V-18V DeWALT Batteries	9.6V-18V DeWALT Batteries	3 D-Size Alkaline	3 D-Size Alkaline	3 D-Size Alkaline
Accuracy per 100 ft.	±1/4 in	±1/4 in	±1/4 in	±1/4 in	±1/4 in
Indoor Visibility Range	200 (dia) ft	200 (dia) ft	200 (dia) ft	200 (dia) ft	200 (dia) ft
Range with Detector	600 (dia) ft	600 (dia) ft	600 (dia) ft	600 (dia) ft	600 (dia) ft
Rotation Speed	0-600 rpm	0-600 rpm	0-600 rpm	0-600 rpm	0-600 rpm
Laser Class	IIIa (<5mW) @ 635nm	IIIa (<5mW) @ 635nm	IIIa (<5mW) @ 635nm-650nm	IIIa (<5mW) @ 635nm-650nm	IIIa (<5mW) @ 635nm-650nm
Protected Head	Yes	Yes	Yes	Yes	Yes
Roll Bar / Bump Sensor	Yes / Yes	Yes / Yes	Yes / Yes	Yes / Yes	Yes / Yes
Tool Weight	8.9 lbs	8.9 lbs	6.6 lbs	6.6 lbs	6.6 lbs
Includes	1 hour charger, 18V battery, laser target card, laser enhancement glasses	same as DW073K plus digital laser detector and clamp	laser target card	same as DW071K plus wall mount and laser enhancement glasses	same as DW071K plus digital laser detector and clamp

LASERS



SPECIFICATIONS	DW087K	DW086K	DW084K	DW082K	DW099
Power Supply	3 "AA" batteries	3 "AA" batteries	4 "AA" Alkaline	4 "AA" Alkaline	3 "AA" Alkaline batteries
Accuracy	±1/8" @ 30 ft	±1/8" @ 30 ft	±1/4" @ 100 ft	±1/8" @ 50 ft	±1/4" @ 75 ft
Self-Leveling Range	5°	5°	N/A	N/A	N/A
Indoor Visibility Range	±50 ft	±50 ft	±100 ft	±100 ft	±100 ft
Laser Class	II	II	II (<1mW) @ 635nm	II (<1mW) @ 635nm	II
Includes	3 (AA) batteries 20+ hours run-time	same as DW087K	4 (AA) batteries	4 (AA) batteries	

LASER ACCESSORIES

- DW0714 - Laser Enhancement Glasses
- DW0730 - Laser Target Card
- DW0732 - Digital Laser Detector and Clamp
- DW0734 - Construction Grade Rod
- DW0736 - Construction Tripod
- DW0772 - Digital Laser Detector & Clamp

OPTICAL INSTRUMENTS



SPECIFICATIONS	DW090PK	DW092PK	DW096PK
Leveling Type	Manual	Manual	Auto
Accuracy per 100 ft.	±1/4 in	±1/4 in	±1/32 in
Magnification	20x	20x	26x
Range	200 ft	200 ft	300 ft
Stadia Ratio	1:100	1:100	1:100
Horizontal Circle Type	Continuous Drive	Continuous Drive	Continuous Drive
Each include an aluminum tripod w/quick adjust legs and 8' aluminum grade rod (feet-inches-eighths)			

TILE LASER



SPECIFICATIONS	DW060K
Accuracy per 25 ft.	+/- 1/8 in
Operating range	Up to 100' ft
Operating Temperature	0-45 °C
Battery Life	70 hrs

18 < PREVIOUS

www.DeWALT.com

1-800-4 DEWALT

NEXT >