



# CORDLESS POWER TOOLS

**GUARANTEED TOUGH.**

## ROTARY LASERS



**18V Self-Leveling Int/Ext Rotary Laser Package**



**Self Leveling Interior Rotary Laser - Combo Kit**



**Self Leveling Rotary Laser - Combo Kit w/Detector (Int/Ext)**



**Self-Leveling Int/Ext Rotary Laser Kit**

SPECIFICATIONS	DW079KDT	DW079KI	DW079KD	DW074KDT
Power Supply	96V-18V DeWALT batteries	96V-18V DeWALT batteries	96V-18V DeWALT batteries	(2) D Alkaline batteries
Accuracy per 100 ft.	1/8"	1/8"	1/8"	1/4"
Rotation Speed	0, 60, 250, & 600 rpm	0, 60, 250, & 600 rpm	0, 60, 250, & 600 rpm	0, 60, & 600 rpm
Self-Leveling Range	±5°	±5°	±5°	±5°
Indoor Visibility Range	200 (dia) ft	200 (dia) ft	200 (dia) ft	100 (dia) ft
Range with Detector	2000 (dia) ft	2000 (dia) ft	2000 (dia) ft	800 (dia) ft
Laser Class	IIIa (<5mW)at 635nm	IIIa (<5mW)at 635nm	IIIa (<5mW)at 635nm	IIIa (<5mW)at 635nm
Slope (Single Axis)	Minus Slope ±5°	Minus Slope ±5°	Minus Slope ±5°	-
Charger/Batteries	1 Hour Charger / (1) 18V	1 Hour Charger / (1) 18V	1 Hour Charger / (1) 18V	-
Includes	Wall mount, wireless (IR) remote control, laser target card, laser enhancement glasses, construction tripod - DW0736	Wall mount, wireless (IR) remote control, laser target card, laser enhancement glasses	Wall mount, wireless (IR) remote control, laser target card, laser enhancement glasses, digital laser detector	DW0742 Detector and clamp, Target card, DW0740 Wall mount, DW0737 Tripod, DW0748 8' grade rod, (2) D Alkaline batteries, & (1) 9V battery



**Self-Leveling Int/Ext Rotary Laser Kit**



**Self Leveling 3Beam Line Laser**



**Self-Leveling Line Laser (Horizontal and Vertical)**



**Self Leveling Level, Plumb, & Square, 4 Beam Laser**



**Laser Plumb Bob**

SPECIFICATIONS	DW074KD	DW089K	DW087K	DW084K	DW082K
Power Supply	2 D Alkaline batteries	(4) AA batteries	(8) AA batteries	(4) AA batteries	(4) AA batteries
Accuracy per 100 ft.	1/4"	1/8in. @30 Ft	1/8in. @30 Ft	1/4"	1/4"
Rotation Speed	0, 60, & 600 rpm	-	-	-	-
Self-Leveling Range	±5°	±5°	±5°	±1/4" @ 100	±1/8" @ 50
Indoor Visibility Range	100 (dia) ft	10 (dia) ft	50 (dia) ft	100 (dia) ft	100 (dia) ft
Range with Detector	600 (dia) ft	-	-	-	-
Laser Class	IIIa (<5mW)at 635nm	II	II	I (<1mW) at 635nm	I (<1mW) at 635nm
Slope (Single Axis)	-	-	-	-	-
Charger/Batteries	-	(4) AA batteries	(8) AA batteries	-	-
Tool Weight	45 lbs	1.9 lbs	1.2 lbs	1.2 lbs	12 lbs
Includes	DW0742 Digital laser detector, DW0740 Wall mount, Target card, (2) D size Alkaline batteries	Ceiling mount	Ceiling mount	-	-

## OPTICAL INSTRUMENTS



**PAGE 40**

## VACUUMS



**18V Cordless 1/2 Gallon Wet/Dry Portable Vac**



**18V Cordless 1/2 Gallon Wet/Dry Portable Vac (Tool Only)**



**2 Gallon Cordless/Corded Wet/Dry Vac**

SPECIFICATIONS	DC515K	DC515B	DC500
Tank Size	1/2 gallon	1/2gallon	2gallon
Inlet Diameter	1-1/4"	1-1/4"	1-1/4"
Inlet Length	2.5'	2.5'	5'
Voltage (DC Operation)	18V	18V	12-18V
Blower	No	No	Yes
Weight	6.0 lbs	3.6 lbs	9.0 lbs
Charger/Batteries	1 Hour Charger / (1) 18V XRP™	Sold Separately	Sold Separately
Includes	-	-	5 heavy-duty rubberhose, crevice tool, & wide nozzle