

## POWER TOOLS

**GUARANTEED TOUGH.**

### SCREWDRIVERS



5,300 rpm  
High Speed VSR  
Drywall Scrugun



4,000 rpm  
Lightweight VSR  
Drywall Scrugun



4,000 rpm  
Heavy-Duty VSR  
Drywall Scrugun



2,500 rpm  
VSR All-Purpose  
Scrugun

SPECIFICATIONS	DW255	DW252	DW272/W/WT	DW257
Amps	6.0 Amps	6.0 Amps	6.3 Amps	6.2 Amps
No Load Speed	0-5,300 rpm	0-4,000 rpm	0-4,000 rpm	0-2,500 rpm
Clutch	Standard	Standard	Standard	Standard
Torque	60 in.-lbs	60 in.-lbs	81 in.-lbs	132 in.-lbs
Max Fastener Size	#8	#8	#8	#12
Tool Weight	2.9 lbs	2.8 lbs	3.1 lbs	3.5 lbs

W = 50 ft. cord  
WT = 50 ft. twist lock cord



2,500 rpm  
Heavy-Duty VSR  
All-Purpose Scrugun



2,500 rpm  
VSR Depth-Sensitive  
TEKS® Scrugun



2,500 rpm  
Lightweight VSR All-Purpose  
Scrugun with Kit Box



2,000 rpm  
VSR VERSA-CLUTCH™  
Scrugun

SPECIFICATIONS	DW276	DW266	DW260K	DW267
Amps	6.5 Amps	6.5 Amps	6.2 Amps	6.5 Amps
No Load Speed	0-2,500 rpm	0-2,500 rpm	0-2,500 rpm	0-2,000 rpm
Clutch	Standard	Standard	Standard	VERSA-CLUTCH™ System
Torque	132 in.-lbs	132 in.-lbs	132 in.-lbs	164 in.-lbs
Max Fastener Size	#14	#14	#12	#14
Tool Weight	3.6 lbs	3.5 lbs	3.2 lbs	3.7 lbs

1/4", 5/16", 3/8" Nut Setters,  
3 Locators and Kit Box



2,500 rpm  
VSR VERSA-CLUTCH™  
Scrugun



1,000 rpm  
VSR VERSA-CLUTCH™  
Scrugun



2,500 rpm  
VSR Positive-Clutch Scrugun  
with 1/4" Bit Holder



2,500 rpm  
VSR Positive-Clutch Scrugun  
with Threaded Clutch Housing

SPECIFICATIONS	DW268	DW269	DW281	DW284
Amps	6.5 Amps	6.5 Amps	6.5 Amps	6.5 Amps
No Load Speed	0-2,500 rpm	0-1,000 rpm	0-2,500 rpm	0-2,500 rpm
Clutch	VERSA-CLUTCH™ System	VERSA-CLUTCH™ System	Positive	Positive
Torque	132 in.-lbs	314 in.-lbs	132 in.-lbs	132 in.-lbs
Max Fastener Size	#14	#14	#14	#14
Tool Weight	3.7 lbs	3.7 lbs	3.4 lbs	3.3 lbs

1-800-4DEWALT

**CORDED POWER TOOLS** 27