

ACCESSORIES

GUARANTEED TOUGH.

CONSTRUCTION SAW BLADES

PORTABLE



CAT #	DESCRIPTION	KERF TYPE	DIA.	TEETH	ARBOR	HOOK ANGLE	KERF	PLATE THICKNESS	TOOTH GRIND
Carbide Tipped									
DW3161	Circular Saw Blade	Thin Kerf	6-1/2"	18	5/8" - \diamond	25°	.071"	.045"	ATB
DW3192	Circular Saw Blade	Thin Kerf	7-1/4"	18	5/8" - \diamond	15°	.071"	.045"	ATB
DW3592B10	Circular Saw Blade (BULK)	Thin Kerf	7-1/4"	18	5/8" - \diamond	15°	.071"	.045"	ATB
DW3174	Pressure Treated/Wet Lumber	Thin Kerf	7-1/4"	20	5/8" - \diamond	25°	.071"	.045"	ATB
DW3178	Framing Blade	Thin Kerf	7-1/4"	24	5/8" - \diamond	18°	.071"	.045"	ATB
DW3578B10	Framing Blade (BULK)	Thin Kerf	7-1/4"	24	5/8" - \diamond	18°	.071"	.045"	ATB
DW3176	Circular Saw Blade	Thin Kerf	7-1/4"	36	5/8" - \diamond	15°	.071"	.045"	ATB
DW3576B10	Circular Saw Blade (BULK)	Thin Kerf	7-1/4"	36	5/8" - \diamond	15°	.071"	.045"	ATB
DW3182	Framing Blade	Thin Kerf	8-1/4"	24	5/8" - \diamond	20°	.076"	.050"	ATB
DW3582B10	Framing Blade (BULK)	Thin Kerf	8-1/4"	24	5/8" - \diamond	20°	.076"	.050"	ATB
DW3184	Circular Saw Blade	Thin Kerf	8-1/4"	40	5/8" - \diamond	15°	.076"	.050"	ATB
Specialty Applications									
DW3191	Nail Cutting Circular Saw Blade	Thin Kerf	7-1/4"	18	5/8" - \diamond	15°	.071"	.045"	ATB
DW3591B10	Nail Cutting Circular Saw Blade (BULK)	Thin Kerf	7-1/4"	18	5/8" - \diamond	15°	.071"	.045"	ATB
DW3193	PCD Diamond Fiber Cement Blade (HARDI PLANK® & HARDI BOARD®)	-	7-1/4"	6	5/8"	-5°	.090"	.060"	FTG



CORDLESS



CAT #	DESCRIPTION	DIA.	TEETH	ARBOR	HOOK ANGLE	KERF	PLATE THICKNESS	TOOTH GRIND
DW9052	Carbide - Aluminum/Non-Ferrous Metals	5-3/8"	30	10mm	3°	.059"	.039"	FTG
DW9152	Carbide - Aluminum Cutting	6-1/2"	36	5/8"	3°	.059"	.039"	FTG
DW9053	Steel - Vinyl/Paneling	5-3/8"	80	5/8"	-10°/-45°	.059"	.039"	Alt. Set
DW9054	Carbide - Smooth Woodcutting	5-3/8"	24	10mm	20°	.059"	.039"	ATB
DW9154	Carbide - Framing	6-1/2"	24	5/8"	20°	.059"	.039"	ATB
DW9055	Carbide - Fast Woodcutting	5-3/8"	16	10mm	20°	.059"	.039"	ATB
DW9155	Carbide - Fast Cutting	6-1/2"	18	5/8"	20°	.059"	.039"	ATB
DW9158	Combo Pack (DW9155 & DW9154)	6-1/2"	18/24	5/8"	20°	.059"	.039"	ATB
DW9059C5	Combo Pack (DW9052, DW9053 & DW9054)	5-3/8"	24/30/78	10mm	20°	.059"	.039"	ATB
DW9058	Combo Pack (DW9052 & DW9055)	5-3/8"	16/30	10mm	3°/20°	.059"	.039"	FTG/ATB
DW9153	Steel - Vinyl/Paneling	6-1/2"	90	5/8"	18°/45°/20°	.059"	.039"	FTG
DW9555	Carbide - Fast Cutting (BULK)	6-1/2"	18	5/8"	20°	.059"	.039"	ATB



LARGE DIAMETER



CAT #	DESCRIPTION	DIA.	TEETH	ARBOR	HOOK ANGLE	KERF	PLATE THICKNESS	TOOTH GRIND
DW3112	Fast Ripping Table Saw Blade	10"	24	5/8"	15°	.095"	.069"	ATB
DW3103	General Purpose Saw Blade	10"	32	5/8"	5°	.095"	.069"	ATB
DW3114	General Purpose Saw Blade	10"	40	5/8"	10°	.095"	.069"	ATB
DW3106	Fine Finish Saw Blade	10"	60	5/8"	5°	.095"	.069"	ATB
DW3123	General Purpose Saw Blade	12"	32	1"	-5°	.095"	.069"	ATB
DW3126	Fine Finish Saw Blade	12"	60	1"	0°	.095"	.069"	ATB
DW3128	Series 20 Circular Saw Blade	12"	80	1"	5°	.095"	.069"	ATB



LARGE DIAMETER COMBO PACKS



CAT #	DESCRIPTION	DIA.	ARBOR	TEETH
DW3106P5	Construction 10" Combo Pack (DW3106 & DW3103)	10"	5/8"	60, 32
DW3128P5	Construction 12" Combo Pack (DW3128 & DW3123)	12"	1"	80, 32


1-800-4DEWALT
HEAVY-DUTY ACCESSORIES

67