

DEWALT High-Speed Steel Spade Bit Set, 4-Piece

Model # DW4SPADE



SPECIFICATIONS

| | | | |
|-------------------------|-----------|-------------------------|---------------------|
| Assembled Depth (in.) | 4.875 in | Assembled Height (in.) | 8.25 in |
| Assembled Width (in.) | 0.46 in | Bit diameter (in.) | 0.25 |
| Color Family | Black | Drill & Router Bit Type | Auger & Spade |
| Drilling depth (in.) | 6 | Item Package Type | Cardboard Container |
| Min Chuck Size Required | 1/4 In. | Power Tool Product Type | Drill & Router Bits |
| Returnable | 90-Day | Shank Diameter | 1/4 In. |
| Type | Spade bit | | |

The DEWALT 4-Piece high-speed steel spade bit set features bits with high-speed steel construction. These bits are designed with heavy-duty 1/4 in. shanks. All 4 bits offer a 6 in. drilling depths.

- 6 in. drilling depth
- High-speed steel construction
- Heavy-duty 1/4 in. shanks
- Set includes 1/2 in., 5/8 in., 3/4 in. and 1 in. bits