

POWER TOOLS

**GUARANTEED
TOUGH.**

THICKNESS PLANERS



13" Three Knife, Two Speed Thickness Planer



12-1/2" Thickness Planer w/ Three Knife Cutter-Head

SPECIFICATIONS	DW735	DW734
Amps	15.0 Amps	15 Amps
Max. Depth of Cut	1/8"	1/8"
Depth Capacity	6"	6"
Width Capacity	13"	12-1/2"
Speeds	2	1
Cuts Per Inch	96 and 179	96
Tool Weight	92 lbs	80 lbs

THICKNESS PLANER ACCESSORIES (DW735)	(DW734)
DW7350 – Mobile Stand	DW7342 – 12-1/2" Disposable, Reversible Knives
DW7351 – 13" Folding Tables	DW7331 – Dust Hood
DW7352 – 13" Disposable, Reversible Knives	
DW7353 – Chip Collector	
DW7352-2 – 13" Vacuum Heat Treated Double Sided Two Pack Replacement Planer Knives	
DW735X – 13" Three Knife, Two Speed Thickness Planer	

MEASURER



Laser Distance Measurer

SPECIFICATIONS	DW030P
Operating Range	100 ft
Accuracy	1/8"
Laser Class	II (<1 mW) @ 635nm
Power Supply	(2) AAA Alkaline Batteries

HAND PLANERS



3-1/4" Planer Kit with 3/32" (2.5mm) Depth of Cut



3-1/4" Portable Hand Planer



3-1/4" Portable Hand Planer Kit

SPECIFICATIONS	DW680K	D26676	D26677K
No Load Speed	15,000 rpm	17,000 rpm	17,000 rpm
Amps	7.0 Amps	5.5 Amps	5.5 Amps
Depth Of Cut (mm)	2.5 mm	1.5 mm	1.5 mm
Depth Of Cut (inches)	3/32"	1/16"	1/16"
Planing Width	3-1/4"	3-1/4"	3-1/4"
Rabbeting Depth	1/2"	23/64"	23/64"
Tool Weight	6.2 lbs	6.0 lbs	6.0 lbs

HAND PLANER ACCESSORIES
— DW6654 – Pair of Reversible Carbide Blades
— DW6655 – High Speed Steel Blades

HEAT GUNS



Heat Gun



Heat Gun



Heat Gun Kit with LCD Display

SPECIFICATIONS	D26950	D26960	D26960K
Watts	1550W	1550W	1550W
Voltage	120V	120V	120V
Amps	13 Amps	13 Amps	13 Amps
Temperature	120° to 1100° F	150° to 1100° F	150° to 1100° F
Max. cfm	16 cfm	17.7 cfm	17.7 cfm
LCD	No	Yes	Yes
Power Cord	10 ft	10 ft	10 ft
Weight	2.1 lbs	2.3 lbs	2.3 lbs

1-800-4-DEWALT

CORDED POWER TOOLS 43