



HEAVY-DUTY POWER TOOLS

GUARANTEED TOUGH.

IMPACT WRENCHES



SPECIFICATIONS	DC800KL	DW059K-2	DW057K-2	DW055K-2	DW053K-2	DW051K-2
1/2" (13mm) 36V High Torque Impact Wrench Kit	1/2" (13mm) 18V High Torque Impact Wrench Kit	1/2" (13mm) 18V Impact Wrench Kit	1/2" (13mm) 14.4V Impact Wrench Kit	1/2" (13mm) 12V Impact Wrench Kit	3/8" (9.5 mm) 12V Impact Wrench Kit	
Voltage	36V	18V	18V	14.4V	12V	12V
Drive	patented shear-resistant 1/2" square	patented shear-resistant 1/2" square	1/2" square w/detent pin retention	1/2" square w/detent pin retention	1/2" square w/detent pin retention	3/8" square w/hog ring retention
No Load Speed	1,400 rpm	1,650 rpm	0-2,400 rpm	0-2,400 rpm	0-2,400 rpm	0-2,400 rpm
Impacts/Min	2,500 bpm	2,600 bpm	0-3,000 bpm	0-3,000 bpm	0-3,000 bpm	0-3,000 bpm
Max... Torque	3,900 in-lbs	3,600 in-lbs	1,650 in-lbs	1,550 in-lbs	1,400 in-lbs	1,200 in-lbs
Max... Torque	325 ft-lbs	300 ft-lbs	138 ft-lbs	129 ft-lbs	117 ft-lbs	100 ft-lbs
Tool Length	10-3/4"	10-3/4"	6-1/2"	6-1/2"	6-1/2"	6-1/2"
Tool Weight	7.5 lbs	7.55 lbs	4.9 lbs	4.1 lbs	3.75 lbs	3.7 lbs
Charger/Batteries	1 hour / (2) 36V	1 hour / (2) 18V XRP™	1 hour / (2) 18V XRP™	1 hour / (2) 14.4V	1 hour / (2) 12V	1 hour / (2) 12V

IMPACT DRIVERS



SPECIFICATIONS	DW056K-2	DW054K-2	DW052K-2	DW050K-2
18V Cordless Impact Driver Kit	14.4V Cordless Impact Driver Kit	12V Cordless Impact Driver Kit	9.6V Cordless Impact Driver Kit	
Voltage	18V	14.4V	12V	9.6V
Drive Size	1/4" hex shank quick release	1/4" hex shank quick release	1/4" hex shank quick release	1/4" hex shank quick release
No Load Speed	0-2,400 rpm	0-2,400 rpm	0-2,400 rpm	0-2,400 rpm
Impacts/Min	0-3,000 bpm	0-3,000 bpm	0-3,000 bpm	0-3,000 bpm
Max... Torque	1,170 in-lbs	1,150 in-lbs	1,000 in-lbs	900 in-lbs
Max... Torque	98 ft-lbs	96 ft-lbs	83 ft-lbs	75 ft-lbs
Tool Length	6-1/2"	6-1/2"	6-1/2"	6-1/2"
Tool Weight	4.9 lbs	4.1 lbs	3.75 lbs	3.5 lbs
Charger/Batteries	1 hour / (2) 18V XRP™	1 hour / (2) 14.4V	1 hour / (2) 12V	1 hour / (2) 9.6V

CIRCULAR SAWS



SPECIFICATIONS	DC300K	DC390K	DW936K
7-1/4" 36V Cordless Circular Saw Kit	18V Cordless Circular Saw Kit	5-3/8" (136mm) 18V Cordless Trim Saw Kit	
Voltage	36V	18V	18V
No Load Speed	4,000 rpm	3,700 rpm	0-3,200 rpm
Blade Diameter	7-1/4"	6-1/2"	5-3/8"
Bevel Capacity	0-50°	0-50°	50°
Depth Of Cut At 90°	2-7/16"	2-1/4"	1-5/8"
Tool Weight	9.9 lbs	8.7 lbs	7.5 lbs
Charger/Batteries	1 hour / (1) 36V	1 hour / (1) 18V XRP™	1 hour / (1) 18V
Includes	carbide tipped blade, rip fence	16 tooth-carbide saw blade, blade wrench, rip fence	5/8" 16-tooth carbide saw blade and blade wrench

METAL CUTTING CIRCULAR SAW



SPECIFICATIONS	DW934K-2
6-3/4" (173mm) 18V Cordless Metal Cutting Circular Saw Kit	
Voltage	18V
No Load Speed	3,200 rpm
Blade Diameter	6-3/4"
Bevel Capacity	N/A
Depth Of Cut At 90°	2-3/8"
Tool Weight	9.5 lbs
Charger/Batteries	1 hour / (2) 18V XRP™
Includes	6-3/4" 40-tooth titanium carbide tipped blade

RIGHT ANGLE DRILL/DRIVERS



SPECIFICATIONS	DW960K-2	DW966K-2	DW965K-2	DW955K-2
3/8" (10mm) 18V Cordless Right Angle Drill/Driver Kit	3/8" (10mm) 14.4V Cordless Right Angle Drill/Driver Kit	3/8" (10mm) 12V Cordless Right Angle Drill/Driver	3/8" (10mm) 9.6V Cordless Right Angle Drill/Driver Kit	
Voltage	18V	14.4V	12V	9.6V
Max. Power	320 UWO	210 UWO	165 UWO	130 UWO
Chuck Size	3/8"	3/8"	3/8"	3/8"
# of Speed Settings	2	2	2	2
No Load Speed	0-500/0-1,500 rpm	0-400/0-1,250 rpm	0-400/0-1,200 rpm	0-400/0-1,100 rpm
Chuck Type	plastic, 2-sleeve	plastic, 2-sleeve	plastic, 2-sleeve	plastic, 2-sleeve
Tool Weight	4.7 lbs	4.4 lbs	4.1 lbs	3.9 lbs
Charger/Batteries	1 hour / (2) 18V	1 hour / (2) 14.4V	1 hour / (2) 12V	1 hour / (2) 9.6V
Includes	screwdriver bit			

2 <PREVIOUS

www.DeWALT.com

1-800-4DEWALT

NEXT >