



HEAVY-DUTY POWER TOOLS

GUARANTEED TOUGH.

HIGH TORQUE WRENCHES



1/2" (13mm) 36V Cordless Li-Ion Impact Wrench Kit



1/2" (13mm) 28V Cordless Li-Ion Impact Wrench Kit



1/2" (13mm) 18V Cordless XRP™ Impact Wrench Kit



1/2" (13mm) 18V Cordless XRP™ Impact Wrench Kit

SPECIFICATIONS	DC800KL	DC810KL	DC821KA	DW059K-2
Voltage	36V	28V	18V	18V
Drive Size	1/2"	1/2"	1/2" square with detent pin retention	1/2" square with detent pin retention
No Load Speed	1,400 rpm	2,400 rpm	0-2,100 rpm	1,650 rpm
Impacts/Min	2,500 ipm	3,000 ipm	0-3,000 ipm	2,600 ipm
Max. Torque	in-lbs	1,920 in-lbs	1,920 in-lbs	3,600 in-lbs
Max. Torque	325 ft-lbs	160 ft-lbs	160 ft-lbs	300 ft-lbs
Tool Weight	7.5 lbs	5.0 lbs	5.3 lbs	7.55 lbs
Tool Length	10-3/4"	7-5/8"	7-5/8"	10-3/4"
Charger/Batteries	1 hour / (2) 36V Li-Ion	1 hour / (2) 28V Li-Ion	1 hour / (2) 18V XRP™	1 hour / (2) 18V XRP™

RIGHT ANGLE DRILLS/DRIVERS



3/8" (10mm) 18V Cordless Right Angle Drill/Driver Kit



3/8" (10mm) 18V Cordless Li-Ion Right Angle Drill Kit



3/8" (10mm) 14.4V Cordless Right Angle Drill/Driver Kit



3/8" (10mm) 12V Cordless Right Angle Drill/Driver Kit

SPECIFICATIONS	DW960K-2	DCD690KL	DW966K-2	DW965K-2
Voltage	18V	18V	14.4V	12V
Max Power	320 UWO	270 UWO	210 UWO	165 UWO
Chuck Size	3/8"	3/8"	3/8"	3/8"
# Of Speed Settings	2	2	2	2
RPM	0-500/0-1,500	0-500/0-1,500	0-400/0-1,250	0-400/0-1,200
Chuck Type	plastic, ratcheting	plastic, ratcheting	plastic, ratcheting	plastic, ratcheting
Tool Weight	4.7 lbs	3.9 lbs	4.4 lbs	4.1 lbs
Charger/Batteries	1 hour / (2) 18V	30 min / (2) 18V Compact Li-Ion	1 hour / (2) 14.4V compact	1 hour / (2) 12V compact
Includes	screwdriver bit	screwdriver bit		

SDS ROTARY HAMMERS



18V 7/8" (22mm) Cordless SDS Hammer Kit



24V 7/8" (22mm) Cordless SDS Hammer Kit



28V 1" (25mm) Cordless Li-Ion SDS Rotary Hammer Kit



36V 1" (25mm) Cordless Li-Ion SDS Rotary Hammer Kit

SPECIFICATIONS	DC212KA	DC223KA	DC228KL	DC233KL
Concrete Optimum	5/32" - 1/2"	5/32" - 1/2"	5/32" - 5/8"	5/32" - 5/8"
Impact Energy	1.7 ft-lbs	1.7 ft-lbs	1.9 ft-lbs	1.9 ft-lbs
No Load Speed	0-1,100 rpm	0-1,100 rpm	0-1,150 rpm	0-1,150 rpm
Beats/Min	0-4,100 bpm	0-4,100 bpm	0-4,400 bpm	0-4,400 bpm
Chipping	No	Yes	Yes	Yes
Vibration Control	Yes - SHOCKS™	Yes - SHOCKS™	Yes - SHOCKS™	Yes - SHOCKS™
Tool Length	10.5"	10.5"	10.5"	10.5"
Tool Weight	7.6 lbs	8.4 lbs	7.6 lbs	7.8 lbs
Charger/Batteries	1 hour / (2) 18V XRP™	1 hour / (2) 24V	1 hour / (2) 28V Li-Ion	1 hour / (2) 36V Li-Ion
Warranty - Service Contract	1 Yr	1 Yr	1 Yr	1 Yr

SCREWDRIVERS



18V Cordless XRP™ Light Gauge Steel Framing Screwdriver Kit



18V Cordless Drywall/Deck Screwdriver Kit



12V Cordless Drywall/Deck Screwdriver Kit



1/4" (6mm) 7.2V Cordless Two-Position Screwdriver Kit

SPECIFICATIONS	DC668KA	DC520KA	DW979K-2	DW920K-2
Voltage	18V	18V	12V	7.2V
No Load Speed	0-900/0-2,700 rpm	0-900/0-2,900 rpm	0-800/0-2,300 rpm	0-500 rpm
Max. Torque	180 in-lbs	180 in-lbs	180 in-lbs	80 in-lbs
Capacity (CRS)	12-28 ga.	12 ga.	12 ga.	-
Tool Weight	5.4 lbs	5.1 lbs	4.2 lbs	3.5 lbs
Drive Size	1/4" Hex	1/4" Hex	1/4" Hex	1/4" Hex
Charger/Batteries	1 hour / (2) 18V XRP™	1 hour / (2) 18V XRP™	1 hour / (2) 12V	1 hour / (2) 7.2V compact
Includes	#2 Phillips screwdriver bit, 5/16" nut runner	bit tip/magnetic holder, drywall nosepiece, TEKS® nosepiece	bit tip/magnetic holder, drywall nosepiece, TEKS® nosepiece	2 screwdriver bits

1-800-4 DEWALT

Text "DEWALT" to 32075 to be the first to know about anything DEWALT