



# CORDLESS POWER TOOLS

**GUARANTEED TOUGH.**

**IMPACT DRIVERS & WRENCHES**



**3/8" (9.5mm) 18V Cordless Impact Wrench Kit**



**3/8" (9.5mm) 18V Cordless Impact Wrench (Tool Only)**



**18V Cordless Impact Wrench**



**1/2" (13mm) 18V Cordless Impact Wrench Kit**

SPECIFICATIONS	DC823KA	DC823B	DC822KL	DC820KA
Volts	18V	18V	18V	18V
Drive Size	3/8" square w/ hog ring anvil	3/8" square w/ hog ring anvil	1/2" square w/ detent pin anvil	1/2" square w/ detent pin anvil
No Load Speed	0-2,400 rpm	0-2,400 rpm	0-2,400 rpm	0-2,400 rpm
Impacts/Min	0-2,700 ipm	0-2,700 ipm	0-2,700 ipm	0-2,700 ipm
Torque (ft-lbs)	1,500 in-lbs	1,500 in-lbs	1,740 in-lbs	1,740 ft-lbs
Torque (ft-lbs)	125 ft-lbs	95 ft-lbs	145 ft-lbs	145 ft-lbs
Tool Length	5-3/4"	5-3/4"	5-3/4"	5-3/4"
Weight	4.6 lbs	22 lbs (tool only)	3.7 lbs	4.6 lbs
Charger/Batteries	1 Hour Charger / (2) 18V XRP™	Sold Separately	1 Hour Charger / (2) 18V XRP™ Li-Ion	1 Hour Charger / (2) 18V XRP™
Includes	-	-	-	-



**1/2" (13mm) 18V Cordless Impact Wrench (Tool Only)**



**1/4" (6.35mm) 14.4V Cordless Impact Driver Kit**



**1/2" (13mm) 14.4V Cordless Impact Wrench Kit**



**12V MAX\* 1/4" Impact Driver Kit**

SPECIFICATIONS	DC820B	DC835KA	DC830KA	DCF815S2
Volts	18V	14.4V	14.4V	12V MAX*
Drive Size	1/2" square w/ detent pin anvil	1/4" hex shank quick release	1/2" square w/detent pin anvil	1-handed loading, 1/4" hex chuck
No Load Speed	0-2,400 rpm	0-2,400 rpm	0-2,400 rpm	0-2,450 rpm
Impacts/Min	0-2,700 ipm	0-2,700 ipm	0-2,700 ipm	0-3,400 ipm
Torque (ft-lbs)	1,740 in-lbs	1,240 in-lbs	1,620 in-lbs	950 ft-lbs
Torque (ft-lbs)	145 ft-lbs	103 ft-lbs	135 ft-lbs	79 ft-lbs
LEDs	-	-	-	3
Tool Length	5-3/4"	5-3/4"	5-3/4"	6-1/4"
Weight	2.2 lbs (tool only)	3.9 lbs	3.9 lbs	2.3 lbs
Charger/Batteries	Sold Separately	1 Hour Charger / (2) 14.4V XRP™	1 Hour Charger / (2) 14.4V XRP™	Fast Charger / (2) 12V MAX* Lithium Ion
Includes	-	-	-	1) Impact Readybit Tip & (1) belt hook



**12V MAX\* 3/8" Impact Wrench Kit**



**1/4" (6.35mm) 12V Cordless Impact Driver Kit**



**3/8" (9.5 mm) 12V Cordless Impact Wrench Kit**

SPECIFICATIONS	DCF813S2	DC845KA	DC841KA
Volts	12V MAX*	12V	12V
Drive Size	3/8" Anvil	1/4" hex shank quick release	3/8" square w/ hog ring retention
Max Power	-	-	-
No Load Speed	0-2,450 rpm	0-2,400 rpm	0-2,400 rpm
Impacts/Min	0-3,400 ipm	0-2,700 ipm	0-2,700 ipm
Torque (ft-lbs)	1,150 in-lbs	1,150 in-lbs	1,260 in-lbs
Torque (ft-lbs)	96 ft-lbs	96 ft-lbs	105 ft-lbs
LEDs	3	-	-
Tool Length	6-1/4"	5-3/4"	5-3/4"
Weight	2.3 lbs	3.6 lbs	3.6 lbs
Charger/Batteries	Fast Charger / (2) 12V MAX* Lithium Ion	1 Hour Charger / (2) 12V XRP™	1 Hour Charger / (2) 12V XRP™
Includes	-	-	-